

PHILIPS

Vacuum cleaner
with bag

Performer

EnergyCare

RemoteControl

FC9179/01



Greener every day

Save 35% energy with highly efficient HD motor*

The highest suction power ever, resulting in effortless cleaning: this is what the Philips Performer is all about. The new highly efficient HD motor uses up to 35% less energy, while keeping the excellent suction power.

Low power consumption, high-power results

- New 1250 Watt HD motor generates max. 375 Watt suction power

Less waste in the environment

- At least 60% of plastics are sustainable

Helps prevent strain on back and wrists

- Unique ergonomically designed PostureProtect handle

Change controls without bending down

- Fingertip controls in the handle

Highly efficient anti-allergy system


- HEPA AirSeal plus HEPA 13 washable filter



asimpleswitch.com

Highlights

New 1250 Watt HD motor



Highly efficient 1250 Watt HD (High Density) motor generates 375 Watt max. suction power, which means that you use 35% less energy without giving in on the cleaning result.

PostureProtect handle

The patented PostureProtect handle offers you a 4 x better body posture: it helps to prevent bending while cleaning; it supports keeping your wrist in a comfortable position; both handles make manoeuvring easy; and you can regulate the vacuum cleaner with fingertip controls.

Fingertip controls



Via the buttons in the handle you can easily operate your vacuum cleaner — without bending!

Tri-active nozzle



This unique nozzle is aerodynamically designed for maximum cleaning efficiency, has side brushes to remove dust from corners and curves, and has a front opening to pick up the big bits. Each stroke will deliver an immediate clean result.

HEPA AirSeal, HEPA 13 filter



This vacuum cleaner has been designed in such a way that all the air taken in is passed through the washable HEPA 13 filter (99.95% filtration) before it is exhausted. No escape is possible.

Specifications

Design

Colour: Greige

Filtration

Dust bag type: s-bag
 Dust capacity: 4 l
 Exhaust filter: Ultra Clean Air HEPA 13 washable filter
 HEPA AirSeal

Nozzles and accessories

Accessories: Crevice tool, Small nozzle
 Accessory storage: On handgrip
 Standard nozzle: TriActive nozzle

Performance

Airflow (max): 39 l/s
 Input power (IEC): 1250 W
 Input power (max): 1250 W
 Noise level (Lc IEC): 76 dB
 Suction power (max): 375 W
 Vacuum (max): 28 kPa

Usability

Action radius: 12 m
 Carrying handle: Top and front
 Clean Comfort cassette
 Cord length: 9 m
 Tube coupling: Button
 Dust bag full indicator
 Power control: Electronic on handgrip
 Tube type: Metal lacquered 2-piece telescopic tube
 Wheel type: Rubber

Weight and dimensions

Weight of product: 6.5 kg

