

PHILIPS

Vacuum cleaner
with bag

PerformerPro

2100W

AirflowMax technology

HEPA 12 filter

FC9184/11



Highest suction power, even as the bag fills up* with 2100W motor and 5L dust capacity

With its powerful 2100W motor and specially designed dust chamber, Philips PerformerPro maintains high airflow, giving you the highest suction power. For great cleaning results, even as the bag fills up!*

Excellent cleaning results

- 2100 Watt motor generating max. 475W suction power
- Specially designed 5L dust compartment for extreme suction
- TriActive nozzle with unique 3-in-1 action

Integrated Anti-Allergy system

- EPA 12 filter with 99.5% filtration of dust
- s-bag Ultra Long Performance captures even more fine dust

Convenience

- 360Flex hose swivel for smooth maneuvering
- Extra long grip with air slide for farther reach

Highlights

2100 Watt motor



2100 W motor generates max. 475W suction power for excellent cleaning results.

5L dust capacity



The specially designed 5L dust chamber maximizes airflow, allowing the dustbag to unfold uniformly, so you get the highest suction power, even as the bag fills-up.

TriActive nozzle



The TriActive nozzle cleans your floor in 3 ways in one go: 1) A larger opening at the tip of the nozzle easily sucks up big bits. 2) It has

maximum cleaning efficiency due to optimized airflow through the nozzle. 3) The two side brushes sweep up the dust and dirt closely alongside furniture and walls.

EPA 12 filter



This special outlet filter captures 99.5% of the dust before the air is blown back into your room, ensuring a clean, dust-free, environment.

s-bag Ultra Long Performance



The Philips s-bag Ultra Long Performance made of five layers of high quality, non-clogging material captures even the finest dust. This excellent filtration gives you a better cleaning result and clean air in your home. The multilayer filtration also maintains the vacuum cleaners high suction power during the entire lifetime of the bag. The s-bag ULP has been tested and certified by the independent test institute TÜV Rheinland Group, proven to last up to 80% longer than a standard dustbag.

Specifications

Design

Color: Star blue

Performance

Airflow (max): 47 l/s
Input power (IEC): 1800 W
Input power (max): 2100 W
Noise level (Lc IEC): 79 dB
Suction power (max): 375, 475 W
Vacuum (max): 35 kPa

Filtration

Dust bag type: s-bag Ultra Long Performance
Exhaust filter: Super Clean Air HEPA 12 filter
Motor filter: Triple layer
Dust capacity: 5 L

Usability

Tube type: Metal 2-piece telescopic tube
Handgrip: Ergonomic grip with air slider
Carrying handle: Top and front
Dust full indicator
Tube coupling: Conical
Park or storage assist: Vertical and horizontal
Wheel type: Rubber
Power control: Electronic on appliance
Action radius: 9 m
Cord length: 6 m

Nozzles and accessories

Standard nozzle: TriActive nozzle
Accessories included: Crevice tool, Small nozzle
Accessory storage: On tubeclip

Weight and dimensions

Weight of product: 5.0 kg
Dimensions of product (LxWxH): 500 x 310 x 300 mm

