

# PHILIPS

Bagless vacuum cleaner


Marathon

2000W

350W suction power

HEPA 12 filter

Parquet



FC9204/01



## Professional cleaning

with high cleaning power that lasts and lasts

Thanks to Philips' new Cyclone Filter technology, the bagless Marathon delivers suction power that lasts. Its efficient design and 2000 W motor deliver very high max. suction power in its category, and it's the quietest bagless available.

### Thorough cleaning results all the time

- 2000 Watt motor generating max. 350 Watt suction power
- High performance cyclone filter for lasting suction power

### Traps dust and allergens inside

- EPA 12 filter with 99.5% filtration of dust

### Superior hard-floor cleaning

- Super Parquet nozzle removes 3 x more sticky dirt

### Easy cleaning, even around furniture

- TriActive nozzle with unique 3-in-1 action

# Highlights

## Super Parquet nozzle



The Super Parquet nozzle allows you really clean hard floors of all kinds in one go, without the risk of harming them. Using the absorption capacity of the micro-fibre pads, together with the suction power of the vacuum cleaner, you achieve maximum result without requiring any detergents or brushes.

## TriActive nozzle



The TriActive nozzle cleans your floor in 3 ways in one go: 1) A larger opening at the tip of the nozzle easily sucks up big bits. 2) It has maximum cleaning efficiency due to optimized airflow through the nozzle. 3) The two side brushes sweep up the dust and dirt closely alongside furniture and walls.

# Specifications

## Design

Color: Black

## Filtration

Exhaust filter: Super Clean Air HEPA 12 filter

Dust capacity: 2 L

## Nozzles and accessories

Accessories included: Brush, Crevice tool, Small nozzle

Accessory storage: On handgrip

Additional nozzle: Super Parquet nozzle

Standard nozzle: TriActive nozzle

## Performance

Airflow (max): 40 l/s

Input power (IEC): 1800 W

Input power (max): 2000 W

Noise level (Lc IEC): 76 dB

Suction power (max): 350 W

Vacuum (max): 30 kPa

## Usability

Carrying handle: Top and front

Tube coupling: Button

Power control: Electronic on appliance

Tube type: Metal lacquered 2-piece telescopic tube

Wheel type: Rubber

Action radius: 12 m

Cord length: 9 m

## Weight and dimensions

Weight of product: 7.2 kg

