

# PHILIPS

Bagless vacuum cleaner

Marathon

PerfectCare



FC9208/01



## Professional cleaning

with high cleaning power that lasts and lasts

Thanks to Philips' new Cyclone Filter technology, the bagless Marathon delivers suction power that lasts. Its efficient design and 2000 W motor deliver very high max. suction power in its category, and it's the quietest bagless available.

### **Thorough cleaning results all the time**

- 2000 Watt motor generating max. 350 Watt suction power
- High performance cyclone filter for lasting suction power

### **Easy cleaning even around furniture**

- TriActive nozzle with unique 3-in-1 action

### **Traps dust and allergens inside**

- HEPA 12 filter with 99.5% filtration of dust

### **Right tool for each type of floor**

- Turbo nozzle removes 25% more hairs and fluff
- Super Parquet nozzle removes 3 x more sticky dirt

# Highlights

## TriActive nozzle

The TriActive nozzle cleans your floor in 3 ways in one go: 1) A larger opening at the tip of the nozzle easily sucks up big bits. 2) It has maximum cleaning efficiency due to optimised airflow through the nozzle. 3) The two side brushes sweep up the dust and dirt closely alongside furniture and walls.

## Turbo nozzle



The turbo brush nozzle removes 50% more fluff from carpets than standard nozzles. The rotating brushes also restore the pile during every cleaning job, keeping carpets and rugs in optimum condition.

# Specifications

## Design

Colour: Black

## Filtration

Dust capacity: 2 l

Exhaust filter: Super Clean Air HEPA 12 filter

## Nozzles and accessories

Accessories: Brush, Crevice tool, Small nozzle

Accessory storage: On handgrip

Additional nozzle: Parquet nozzle, Turbo brush

Standard nozzle: TriActive nozzle

## Performance

Airflow (max): 40 l/s

Input power (IEC): 1800 W

Input power (max): 2000 W

Noise level (Lc IEC): 76 dB

Suction power (max): 350 W

Vacuum (max): 30 kPa

## Usability

Action radius: 12 m

Carrying handle: Top and front

Cord length: 9 m

Tube coupling: Button

Power control: Electronic on appliance

Tube type: Metal lacquered 2-piece telescopic tube

Wheel type: Rubber

## Weight and dimensions

Weight of product: 7.2 kg

