


PHILIPS

Bagless vacuum cleaner

ErgoFit

RemoteControl



FC9256/01



Maximum comfort, minimum effort

Enjoy a better posture with up to 70% less bending

Feel the relief of a better posture! This Philips vacuum cleaner results in significantly less bending while cleaning and brings you more comfort



Helps to prevent strain on back and wrists

- Unique ergonomically designed PostureProtect handle

Change controls without bending down

- Fingertip controls in the handle

Effortless manoeuvring

- Rotating hose connection for easier manoeuvring

Outstanding suction power

- 2000 Watt motor generating max. 375 Watt suction power

Optimal cleaning power every time

- Hygienic semi-automatic filter-cleaning system

Highlights

PostureProtect handle



The patented PostureProtect handle offers you 4x a better body posture: it helps to prevent bending while cleaning; it supports keeping your wrist in a comfortable position; both handles make manoeuvring easy; and you can regulate the vacuum cleaner with fingertip controls.

Fingertip controls




Via the buttons in the handle you can easily operate your vacuum cleaner – without bending!

Rotating hose connection



This hose has a pivoting connection to the handle and therefore allows for easier manoeuvring and less wrist strain.

Outstanding cleaning power



Very efficient 2000 Watt motor, generating a suction power of max. 375 Watt.

Filter-cleaning system



Effortlessly maintain optimal suction power by unclogging the filter without touching the dust.

Exceptionally silent



The soundlevel of this product is very low within its category.

Specifications

Design

Color: Icy white
Material: Luxe

Filtration

Dust capacity: 1.5 L
Exhaust filter: Ultra Clean Air HEPA 13 washable filter
Filter cleaning system: Manual rattle system
Filter type: Gore-Tex HEPA 10
HEPA AirSeal

Nozzles and accessories

Accessories included: Crevice tool, Small nozzle
Accessory storage: On handgrip
Standard nozzle: TriActive nozzle

Performance

Airflow (max): 37 l/s
Input power (IEC): 1800 W
Input power (max): 2000 W
Noise level (Lc IEC): 76 dB
Suction power (max): 375 W
Vacuum (max): 33 kPa

Usability

Action radius: 11 m
Carrying handle: Top and front
Cord length: 8 m
Tube coupling: Button
Handgrip: PostureProtect handle
Power control: Electronic on handgrip
Tube type: Metal lacquered 2-piece telescopic tube
Wheel type: Rubber

Weight and dimensions

Weight of product: 7.5 kg

