


# PHILIPS

Bagless vacuum cleaner

ErgoFit

AutoClean

ParquetCare



FC9261/01



## Maximum comfort, minimum effort

With ComfortControl handle for easier cleaning

Enjoy more comfortable cleaning

### Helps to prevent strain on wrists

- Ergonomically designed ComfortControl handle

### Change controls without bending down

- Fingertip controls in the handle

### Effortless manoeuvring

- Rotating hose connection for easier manoeuvring

### Outstanding suction power

- 2000 Watt motor generating max. 375 Watt suction power

### Effortlessly maintain optimal suction

- Automatic filter-cleaning system

# Highlights

## ComfortControl handle



This ergonomically designed handle helps to prevent strain on wrists. It offers effortless single handed manoeuvring. Enjoy easier cleaning.

## Fingertip controls




Via the buttons in the handle you can easily operate your vacuum cleaner — without bending!

## Rotating hose connection



This hose has a pivoting connection to the handle and therefore allows for easier manoeuvring and less wrist strain.

## Outstanding cleaning power



Very efficient 2000 Watt motor, generating a suction power of max. 375 Watt.

## Automatic filter-cleaning



Effortlessly maintain optimal suction power with only one touch of a button. This automatic filter-cleaning system unclogs your filter without touching the dust.

## Exceptionally silent



The sound level of this product is very low within its category.

# Specifications

## Design

Colour: Bordeaux red  
Material: Luxe

## Filtration

Dust capacity: 1.5 l  
Exhaust filter: Ultra Clean Air HEPA 13 washable filter  
Filter cleaning system: AutoClean system  
Filter type: Gore-Tex HEPA 10  
HEPA AirSeal

## Nozzles and accessories

Accessories: Crevice tool, Small nozzle  
Accessory storage: On handgrip  
Additional nozzle: Parquet nozzle  
Standard nozzle: Wheeled all-purpose nozzle

## Performance

Airflow (max): 37 l/s  
Input power (IEC): 1800 W  
Input power (max): 2000 W  
Noise level (Lc IEC): 76 dB  
Suction power (max): 375 W  
Vacuum (max): 33 kPa

## Usability

Action radius: 11.5 m  
Carrying handle: Top and front  
Cord length: 8 m  
Tube coupling: Button  
Handgrip: ComfortControl handle  
Power control: Electronic on handgrip  
Tube type: Metal lacquered 2-piece telescopic tube  
Wheel type: Rubber

## Weight and dimensions

Weight of product: 7.9 kg

