

Vacuum cleaner  
with bag

SilentStar

Power

FC9310



## Extremely powerful, surprisingly silent Tough on dust, gentle on your ears

Enjoy a relaxing, undisturbed life at home with Philips SilentStar. Thanks to its unique SilentSeal nozzle, the vacuum cleaner ensures powerful cleaning performance with limited noise.

### **Superior cleaning**

- 2000 Watt motor generating max. 450 Watt suction power

### **Low noise, maximum suction with SilentSeal nozzle**

- Optimal performance and low noise thanks to the SilentSeal nozzle
- Noise reduction as low as 73 dB due to the aerodynamic air channel

### **Highly efficient anti-allergy system**


- HEPA AirSeal plus HEPA 13 washable filter

### **Easy to use all over the house**

- Two comfortable carrying handles for extra convenience


# Highlights

## 2000 Watt motor




Powerful 2000 Watt motor generates the maximum 450 Watt suction power for superior cleaning results

## SilentSeal nozzle




The SilentSeal nozzle contributes to an optimal performance in both low noise and dust and fluff pick up. It is optimally sealed for efficient airflow resulting in the best cleaning performance — made by WesselWerk.

## Aerodynamic air channel



The air channel has been fine tuned to ensure that the air can escape with minimum noise. Additionally, a special motor suspension reduces vibrations.


## HEPA AirSeal, HEPA 13 filter



## HEPA AirSeal & HEPA 13 filter

This vacuum cleaner has been designed in such a way that all the air taken in is passed through the washable HEPA 13 filter (99.95% filtration) before it is exhausted. No escape is possible.

## Comfortable carrying handles



This vacuum cleaner has not one, but two carrying handles. When it is on its wheels, there is a handle on top which enables you to easily move the cleaner around with very little bending. The second handle on the front side of the appliance enables you to comfortably carry it around in an upright position.

# Specifications

## Design

**Colour:** Deep black

## Filtration

**Dust bag type:** S-bag

**Dust capacity:** 3.5 l

**Exhaust filter:** Ultra Clean Air HEPA 13 washable filter

**HEPA AirSeal**

## Nozzles and accessories

**Accessories:** Brush, Crevice tool, Small nozzle

**Accessory storage:** On handgrip

**Standard nozzle:** Quiet SilentSeal nozzle

## Performance

**Airflow (max):** 50 l/s

**Input power (IEC):** 1800 W

**Input power (max):** 2000 W

**Noise level (Lc IEC):** 73 dB

**Suction power (max):** 450 W

**Vacuum (max):** 34 kPa

## Sustainability

**Packaging:** > 90% recycled materials

**User manual:** 100% recycled paper

## Usability

**Action radius:** 11 m

**Carrying handle:** Top and front

**Clean Comfort cassette**

**Cord length:** 8 m

**Tube coupling:** Easy release

**Dust bag full indicator**

**Power control:** Electronic on appliance

**Tube type:** Metal 2-piece telescopic tube

**Wheel type:** Rubber

## Weight and dimensions

**Dimensions of product (LxWxH):** 500 x 290 x 250 mm

**Weight of product:** 6.8 kg