

PHILIPS

Bagless vacuum cleaner

PowerPro Compact

PowerCyclone 4

TriActive nozzle



FC9327/09



Full performance

Less energy consumption

The new Philips PowerPro Compact delivers full cleaning performance thanks to the PowerCyclone 4 technology and the TriActive nozzle, engineered for high dust removal. The dust bucket is easy to empty, with no dust clouds.

Excellent cleaning results

- PowerCyclone 4 technology separates dust and air in one go
- The TriActive nozzle applies 3 cleaning actions in one go

Convenience

- Reach all corners thanks to the extra long ergonomic grip
- Advanced dust container design for easy to emptying

Clean air filter system

- EPA10 filter system with AirSeal for healthy air

Highlights

PowerCyclone 4 Technology



PowerCyclone 4 technology maximizes airflow and performance by separating dirt from air in one go. It delivers remarkable cleaning results through highly efficient steps: 1) Air enters fast into the PowerCyclone thanks to the straight and smooth air inlet. 2) The curved airpass quickly accelerates the air upwards in the cyclonic chamber to separate the dust from the air.

TriActive nozzle



The TriActive nozzle applies 3 cleaning actions in one go: 1) It gently opens the carpet with its specially designed soleplate to remove the dust deep down. 2) It sucks up big bits with its larger opening at the front. 3) It picks up the dust and dirt closely alongside furniture and walls with its left and right side air channels.

Easy to empty dust container



The dust container is perfectly designed to dispose dust without creating a dust cloud. Thanks to its unique shape and smooth surface, dust is collected at one side of the container and evenly glides into the dust bin.

EPA10 Clean air system



EPA10 filter and AirSeal capture the finest dust before the air is blown out for a dust-free environment and clean, healthy air.

Extra long ergonomic grip



This ergonomically shaped grip is convenient in use. Its extra long design gives you farther reach, so you can easily clean hard to reach places.

Specifications

Performance

Airflow (max): 28,4 l/s
 Annual energy consumption: 33.8 kW·h
 Input power (IEC): 750 W
 Sound power level: 79 dB
 Vacuum (max): 17,4 kPa

Usability

Action radius: 8 m
 Carrying handle: Front
 Cord length: 5 m
 Tube type: Metal 2-piece telescopic tube
 Wheel type: Plastic
 Tube coupling: Conical

Design

Color: Star white

Filtration

Dust capacity: 1.5 L
 Exhaust filter: Sponge
 Motor filter: Washable foam inlet filter

Nozzles and accessories

Accessories included: Crevice tool, Small nozzle
 Accessory storage: On tubeclip
 Additional nozzle: Hard floor nozzle
 Standard nozzle: TriActive nozzle

Sustainability

Packaging: > 90% recycled materials
 User manual: 100% recycled paper

Weight and dimensions

Dimensions of product (LxWxH): 406 x 285 x 238 mm
 Weight of product: 4.5 kg

