

PHILIPS

Bagless vacuum cleaner

PowerPro Compact

99.9% dust pick-up

900W

PowerCyclone 5

FC9329/69



Compact, yet powerful

With higher dust pick-up* and PowerCyclone 5

Philips PowerPro Compact picks up more dust* and filters out 99.9% for clean floors and fresh air. Powerful cyclonic action and advanced design put dirt in its place and keep it there to control dust, even while emptying.

Remarkable cleaning results

- PowerCyclone 5 technology separates dust from air
- The TriActive nozzle applies 3 cleaning actions in one go
- 99.9% dust pick-up* to deliver high cleaning
- 900W motor for strong suction power

Effortless cleaning

- ActiveLock couplings easily adjust to every task
- Large wheels for better motion control
- Easily emptied with one hand to control dust
- Soft brush integrated into handle, always ready to use

Clean air filter system

- Allergy H13 filter system captures >99.9% of fine dust

Highlights

Powerful cyclonic action



Exclusive PowerCyclone 5 technology accelerates air in the cyclonic chamber to separate out dust. Powerful swirling action maximizes airflow and performance for remarkable cleaning results.

TriActive nozzle



The TriActive nozzle applies 3 cleaning actions in one go: 1) It gently opens the carpet with its specially designed soleplate to remove the dust deep down. 2) It sucks up big bits with its larger opening at the front. 3) It picks up the dust and dirt closely alongside furniture and walls with its left and right side air channels.

Instantly adjust to any task



ActiveLock couplings mean nozzles and accessories simply snap into place on the telescopic tube during cleaning.

Large wheels - better control



The large wheels provide smooth motion control as you clean.

Simple and tidy to empty



The dust container detaches with one hand and controls dust while emptying thanks to its unique shape and smooth surface.

Soft brush at your fingertips



A dusting brush attachment is built right into the handle so it's always ready to use for furniture, flat surfaces and upholstery.

Allergy H13 filter system



The fully-sealed filtration system captures >99.9% of fine dust particles - including pollen, pet hair and dust mites - for allergy

sufferers and anyone demanding a higher level of hygiene. Filtration level is equivalent to HEPA 13*.

99.9% dust pick-up*



You can vacuum 99.9% of fine dust thanks to powerful suction and high performance nozzles.

High-efficiency 900W motor



Our highly efficient motor generates powerful suction and uses less energy for a thorough clean every time.



IF GOLD DESIGN AWARD 2018

IF award-winning products and projects, concepts and more, selected by the top names in design. For 65 years, the iF DESIGN AWARD has been recognized as an arbiter of quality for exceptional design. The iF label is renowned worldwide for outstanding design services, and the iF DESIGN AWARD is one of the most important design prizes in the world.

Specifications

Performance

Airflow (max): 278 l/s
Input power (IEC): 750 W
Input power (max): 900 W
Sound power level: 76 dB
Vacuum (max): 16.8 kPa

Usability

Action radius: 9 m
Carrying handle: Front
Cord length: 6 m
Tube type: Metal 2-piece telescopic tube
Wheel type: Rubber

Design

Color: Dark Royal Blue

Filtration

Dust capacity: 1.5 L
Exhaust filter: Allergy H13 filter
Motor filter: Washable filter
Filtration level: HEPA13 level**

Nozzles and accessories

Accessories included: Crevice tool, Integrated brush
Accessory storage: On tubeclip
Additional nozzle: Hard floor nozzle
Standard nozzle: TriActive nozzle

Sustainability

Packaging: > 90% recycled materials
User manual: 100% recycled paper

Weight and dimensions

Dimensions of product (LxWxH): 410 x 281 x 247 mm
Weight of product: 4,5 kg
Dimensions of packaging (LxWxH): 525 x 320 x 315 mm

Accessories

Filter replacement kit: FC8010/02

