

PHILIPS

Bagless vacuum cleaner

PowerPro Compact

1900 W

PowerCyclone 5

Allergy H13 filter

EPA 10 filter



FC9352/61

Higher suction power* with PowerCyclone 5 Compact, yet powerful

The new Philips PowerPro Compact vacuum cleaner delivers remarkable cleaning results, thanks to PowerCyclone 5 technology and MultiClean nozzle. The dust container is designed for hygienic emptying.

Remarkable cleaning results

- PowerCyclone 5 technology separates dust and air in one go
- 1900 W motor for strong suction power
- New Multi Clean nozzle for thorough cleaning on all floors
- Turbo Brush nozzle removes 25% more hairs and dust

Effortless cleaning

- Advanced dust container design for hygienic emptying
- ActiveLock couplings to easily adjust to each cleaning task
- Soft brush integrated into handle, always ready to use
- Light weight and compact, giving you the freedom to move
- Large rubber wheels for better motion control

Clean air filter system

- Allergy H13 filter system captures >99.9% of fine dust




Highlights

PowerCyclone 5 Technology



PowerCyclone 5 technology maximizes airflow and performance by separating dirt from air in one go. It delivers remarkable cleaning results through highly efficient steps: 1) Air enters fast into the PowerCyclone thanks to the air inlet design. 2) The curved airpass quickly accelerates the air in the cyclonic chamber to separate the dust from the air. 3) The optimized exit blades separate dirt from the cyclone and into the dust bucket.

1900 Watt motor



1900 W motor generates strong suction power for excellent cleaning results.

Easy to empty dust container



The dust container is carefully designed to dispose collected dirt without creating a dust cloud. It is one-hand operated and thanks to its unique shape and smooth surface, you can easily control the emptying of the dust container.

ActiveLock couplings



The ActiveLock couplings allow you to easily connect and disconnect the different nozzles and accessories from the telescopic tube while cleaning.

Soft brush at your fingertips



A dusting brush attachment is built right into the handle so it's always ready to use for furniture, flat surfaces and upholstery.

Multi Clean nozzle




The new Multi Clean nozzle delivers a thorough cleaning on all types of floors. The nozzle is designed to seal closely to the floor to ensure a good pick-up of even the fine dust.

Turbo Brush nozzle



The Turbo Brush nozzle allows deep cleaning of carpets and quick hair and fluff removal from carpets. The rotating brush actively removes small dust particles and hairs, resulting in a 25% better cleaning performance on carpets. The wheels of the nozzle prevent damage in case of use on hard-floors.

Light weight and compact



You can easily carry and roll the vacuum cleaner around when cleaning thanks to its light weight and small size.



IF GOLD DESIGN AWARD 2018

IF award-winning products and projects, concepts and more, selected by the top names in design. For 65 years, the iF DESIGN AWARD has been recognized as an arbiter of quality for exceptional design. The iF label is renowned worldwide for outstanding design services, and the iF DESIGN AWARD is one of the most important design prizes in the world.

Specifications

Performance

Airflow (max): 37 l/s
Input power (IEC): 1600 W
Input power (max): 1900 W
Sound power level: 82 dB
Suction power (max): 350 W
Vacuum (max): 33 kPa

Usability

Action radius: 9 m
Carrying handle: Front
Cord length: 6 m
Tube type: Metal 2-piece telescopic tube
Wheel type: Rubber
Tube coupling: ActiveLock

Design

Color: Dark Royal Blue

Filtration

Dust capacity: 1.5 L
Exhaust filter: Allergy H13 filter
Motor filter: Washable filter
Filtration level: HEPA13 level**

Nozzles and accessories

Accessories included: Crevice tool, Integrated brush
Accessory storage: On tubeclip
Additional nozzle: Turbo brush
Standard nozzle: MultiClean nozzle

Sustainability

Packaging: > 90% recycled materials
User manual: 100% recycled paper

Weight and dimensions

Dimensions of product (LxWxH): 410 x 281 x 247 mm
Weight of product: 4.5 kg
Dimensions of packaging (LxWxH): 525 x 320 x 315 mm

Accessories

Filter replacement kit: FC8010/02

