

PHILIPS

Bagless vacuum
cleaner

5000 Series

900 W

PowerCyclone 7

Allergy H13 filter

TriActive+ nozzle

FC9553/09



50% more suction power

Captures >99.9 of fine dust*

The Philips Bagless Vacuum 5000 Series achieves maximum deep cleaning results with minimum effort thanks to PowerCyclone 7 technology and TriActive+ nozzle featuring 3 optimized cleaning actions in one.

Superior performance

- 900W motor for high suction power
- 99.9% dust pick-up** to deliver high cleaning performance
- PowerCyclone 7 keeps strong suction power for longer
- TriActive+ nozzle to deliver high performance on all floors
- Power control function to adjust suction power
- Allergy H13 filter system captures >99.9% of fine dust

Effortless cleaning

- Compact design with front and top handle for easy carrying
- Dust container designed for hygienic emptying with one hand
- Soft brush integrated into handle & furniture nozzle
- Soft bumper and rubber wheels to protect furniture



Highlights

High-efficiency 900W motor



High-efficiency 900W motor with over 50,000 RPM, generates high suction power for a deep clean every time. Register at [Philips.com](#) within 3 months of purchase for a free 5-year motor warranty.

99.9% dust pick-up**



TriActive+ nozzle and sustained strong suction power ensure you can vacuum 99.9% of fine dust**.

PowerCyclone 7 Technology



PowerCyclone 7 technology features an aerodynamic design to minimize air resistance and ensure sustained strong suction power. Super accelerated air flow in the cylindrical chamber and unique exit blades effectively cut out the dust from the air.

TriActive+ nozzle



TriActive+ nozzle utilizes 3 cleaning actions in one go. It features a larger opening at the front to suck up larger debris while the specially designed soleplate removes dust from deep within carpets. Air channels and brushes on both sides of the nozzle pick up any dust and dirt alongside walls or furniture.

Power control



Power control function easily adjusts suction for different cleaning tasks, from hard floors to soft furnishings.

Compact and lightweight



Compact and lightweight design ensure both storing and lifting the vacuum is easy. The design includes top and front handles for effortless carrying.

Hygienic dust disposal



Easy-to-empty dust container is designed for hygienic disposal with one hand, to help minimize dust cloud.

Brush & furniture nozzle



Dusting brush tool is built into the handle so it's always ready to use on furniture, flat surfaces and upholstery. Furniture nozzle is designed for optimal cleaning of soft furnishings like cushions, couches and arm chairs, even removing pet hair.



5 years warranty

Register at [philips.com/welcome](#) within 3 months of purchase to enjoy 5-year warranty on the motor for free!



Developed in Europe

Manufactured to Philips' highest quality standards.

Specifications

Performance

Input power (IEC): 899 W
Sound power level: 71-77 dB
Input power (max): 900 W

Usability

Power control: Electronic on appliance
Action radius: 9 m
Carrying handle: Top and front
Tube type: Metal 2-piece telescopic tube
Tube coupling: ActiveLock
Wheel type: Rubber

Design

Color: Star white

Filtration

Dust capacity: 1.5 L
Exhaust filter: Allergy H13 filter
Motor filter: Washable filter
Filtration level: HEPA 13 level***

Nozzles and accessories

Standard nozzle: TriActive+ nozzle
Additional nozzle: Furniture nozzle, Hard floor nozzle
Accessories included: Crevice tool, Integrated brush
Accessory storage: On tubeclip

Sustainability

Packaging: > 90% recycled materials
User manual: 100% recycled paper

Weight and dimensions

Weight of product: 4.5 kg
Dimensions of product (LxWxH): 412 x 280 x 280 mm

Accessories

Filter replacement kit: FC8010/02

