

PHILIPS

Bagless vacuum cleaner

Remote Control



FC9714/61



Now with 40% higher suction power*

Designed for easy dust disposal

Philips PowerPro Expert bagless vacuum cleaner takes cleaning performance to the next level. PowerCyclone 6 and TriActive nozzle ensure exceptional cleaning results on all floors. Specially designed bucket makes emptying effortless.

Exceptional performance

- PowerCyclone 6 for exceptional dust and air separation
- TriActive nozzle with unique 3-in-1 action

Easy dust disposal

- Advanced dust bucket design for easy emptying

Effortless cleaning

- ErgoGrip remote control for No - bend Play and Pause
- Lifetime washable filter
- Lightweight design for maneuverability

Highlights

PowerCyclone 6



The aerodynamic design of PowerCyclone 6 minimizes air resistance and ensures exceptional cleaning performance through 3 highly efficient steps: 1) Air enters fast into the PowerCyclone thanks to the straight and smooth air inlet. 2) The curved airpass quickly accelerates the air upwards in the cyclonic chamber. 3) At the top of the cyclone, the exit blades effectively cut out the dust from the air.

TriActive nozzle



The TriActive nozzle cleans your floor in 3 ways in one go: 1) A larger opening at the tip of the nozzle easily sucks up big bits. 2) It has maximum cleaning efficiency due to optimized

airflow through the nozzle. 3) The two side brushes sweep up the dust and dirt closely alongside furniture and walls.

Easy to empty dust bucket



The dust container is perfectly designed for effortless dust disposal. Thanks to its unique shape and smooth surface, dust is collected at one side of the bucket and evenly glides into the dust bin.

ErgoGrip Remote Control



ErgoGrip remote control enables easy maneuverability of the nozzle in tight spaces. Integrated remote control makes it easy to increase, reduce the power or even turn off the vacuum cleaner.

Lifetime washable filter



The foam filter can be easily washed under the tap for life-long performance.

Lightweight design



Only 5.5 kg lightweight design ensures great maneuverability.

Specifications

Performance

Input power (IEC): 650, 2100 W

Design

Color: Soft bronze

Filtration

Exhaust filter: EPA 12 filter

Usability

Power control: Electronic on appliance

Nozzles and accessories

Standard nozzle: TriActive nozzle

Accessories included: Crevice tool, 2-in-1 brush/small nozzle

Other accessories: ErgoGrip Remote Control

Weight and dimensions

Weight of product: 5.5 kg

Dimensions of product (LxWxH):
505x292x2925 mm

Dimensions of packaging (LxWxH):
650x330x310 mm

Sustainability

Packaging: > 90% recycled materials

User manual: 100% recycled paper

