

PHILIPS

Bagless vacuum cleaner

PowerPro Expert

900 W

PowerCyclone 8

Allergy H13 filter

On board accessories



FC9729/69



Highest suction power with PowerCyclone 8* Allergy H13 filter captures >99.9%** of fine dust

The Philips Bagless Vacuum 7000 Series features our highest ever suction power. Make supreme cleaning effortlessly simple with PowerCyclone 8 technology and TriActive nozzle featuring 3 optimised cleaning actions in one.

Superior performance

- 900 W motor for high suction power
- 99.9% dust pick-up*** to deliver high cleaning performance
- PowerCyclone 8 enables highest suction power for longer
- TriActive nozzle for 3 way thorough cleaning action
- Allergy H13 filter system captures >99.9% of fine dust


Effortless cleaning

- On board accessories: Conveniently stored, always at hand
- Digital power control function to adjust suction power
- Dust container designed for hygienic emptying with one hand
- Soft brush integrated into handle, always ready to use



Highlights

High-efficiency 900 W motor



High-efficiency 900 W motor with over 50,000 RPM, generates high suction power for a superior clean every time. Register at [Philips.co.uk](https://philips.co.uk) within 3 months of purchase for a 5 year motor warranty.

99.9% dust pick-up***



TriActive+ nozzle and extreme suction power ensure you can vacuum 99.9% of fine dust***.

PowerCyclone 8 technology



PowerCyclone 8 technology features a powerful, swirling action to maximise air flow and enable highest suction power. Super accelerated air flow in the cylindrical chamber efficiently separates dust from the air at >185 km/h, ensuring stronger suction power for longer, for immaculate cleaning results.

TriActive nozzle



TriActive nozzle utilises 3 cleaning actions in one go. The specially designed soleplate removes dust from deep within carpets, while the large front opening sucks up big bits. Air channels and brushes on both sides of the nozzle pick up any dust and dirt alongside walls or furniture.

On board accessories



On board accessories are stored conveniently inside the back compartment so they're always easy to access when you need them.

Digital power control



Digital power control function easily adjusts suction power for different cleaning tasks, from hard floors to soft furnishings, with the touch of a button.

Hygienic dust disposal



Easy-to-empty dust container is designed for hygienic disposal with one hand to help minimise dust cloud.

Integrated brush



Dusting brush tool is built into the handle so it's always ready to use on furniture, flat surfaces and upholstery.



IF DESIGN AWARD 2018

IF award-winning products and projects, concepts and more, selected by the top names in design. For 65 years, the iF DESIGN AWARD has been recognised as an arbiter of quality for exceptional design. The iF label is renowned worldwide for outstanding design services and the iF DESIGN AWARD is one of the most important design prizes in the world.



5-year warranty

Register at philips.com/welcome within 3 months of purchase to enjoy 5-year warranty on the motor for free!

Specifications

Performance

Airflow (max): 32.5 l/s
Input power (max): 900 W
Sound power level: 67 – 75 dB

Usability

Action radius: 10 m
Carrying handle: Top and front
Cord length: 7 m
Tube type: Metal 2-piece telescopic tube
Wheel type: Rubber
Tube coupling: ActiveLock
Power control: Electronic on appliance

Design

Colour: Monza Red

Filtration

Dust capacity: 2 l
Exhaust filter: Allergy H13 filter
Motor filter: Lifetime washable filter
Filtration level: HEPA 13 level****

Nozzles and accessories

Accessories included: Crevice tool, Small nozzle, Integrated brush
Accessory storage: On board
Additional nozzle: Hard floor nozzle

Standard nozzle: TriActive nozzle

Extra accessories: Filter replacement: FC8003/01

Sustainability

Packaging: > 90% recycled materials
Stand-by power consumption: < 0.5 W
User manual: 100% recycled paper

Weight and dimensions

Dimensions of product (LxWxH): 505 x 292 x 292 mm
Weight of product: 5.5 kg

