

PHILIPS

Bagless vacuum cleaner

PowerPro Ultimate

2,2L NanoClean

Super Turbo brush



FC9922/09



Full performance with PowerCyclone Mess free dust disposal

The new Philips PowerPro Ultimate bagless vacuum cleaner stands for superior cleaning performance. PowerCyclone 7 enables exceptional dust and air separation. TriActiveMax nozzle is for excellent performance on all floors.

Superior performance

- PowerCyclone 7 keeps strong suction power for longer
- Multi-Purpose nozzle
- SuperTurbo Brush for pet hair-free carpets
- Allergy filter captures more than 99.90% of fine dust

Mess free dust disposal

- NanoClean Technology for mess free dust disposal
- Extra Ergonomic Dust Bucket for controlled emptying

Effortless cleaning

- ErgoGrip remote control for No - bend Play and Pause
- Adjustable, long reach tool for hard-to-reach places
- Long reach tool for difficult to access areas



asimpleswitch.com

Highlights

PowerCyclone 7



The aerodynamic design of PowerCyclone 7 minimizes air resistance and ensures exceptional cleaning performance through 3 highly efficient steps: 1) Air enters fast into the PowerCyclone thanks to the straight and smooth air inlet. 2) The curved airpass quickly accelerates the air upwards in the cyclonic chamber. 3) At the top of the cyclone, the exit blades effectively cut out the dust from the air.

TriActiveMax nozzle



TriActiveMax nozzle perfectly seals to the floor and performs 3 actions in one go to thoroughly clean your floors: 1) A specially designed sole plate gently opens the carpet and removes the dust from deep down. 2) Larger front opening pick up bigger particles. 3) Side brushes ensure perfect cleaning along the plinths.

SuperTurbo Brush



Super TurboBrush perfectly removes pet hair from carpets.

Allergy filter



Developed to meet the specific needs of allergy sufferers and more generally of people demanding a higher level of hygiene.

NanoClean Technology



The new innovative technology is especially developed to prevent the usual dust cloud. The new innovative technology is especially developed to prevent the usual dust cloud. The dust settles at the bottom of the dust bucket rather than staying in the air. When the bucket is opened there is no usual dust cloud.

Extra Ergonomic Dust Bucket



The side of the bucket has a specially designed spout-like shape. This enables to empty the bucket in a controlled manner without spilling the dust.

ErgoGrip Remote Control



ErgoGrip remote control enables easy maneuverability of the nozzle in tight spaces. Integrated remote control makes it easy to increase, reduce the power or even turn off the vacuum cleaner.



5 years warranty

Register at philips.com/welcome within 3 months of purchase to enjoy 5-year warranty on the motor for free!



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Performance

Sound power level: 75 dB
Airflow (max): 27 l/s
Vacuum (max): 17 kPa
Input power (IEC): 650 W

Design

Color: Bright copper

Filtration

Exhaust filter: HEPA13 filter
Motor filter: Lifetime washable filter
Dust capacity: 2.2 L

Usability

Power control: Remote control
Tube type: Aluminium 2-P telescopic tube
Tube coupling: SmartLock
Wheel type: Rubber
Carrying handle: Top and front
Action radius: 11 m
Cord length: 8 m

Nozzles and accessories

Standard nozzle: TriActiveMax nozzle
Additional nozzle: Hard floor nozzle, Super Turbo brush

Accessories included: Crevice tool, 2-in-1 brush/small nozzle

Extra accessories: Remote control

Sustainability

Packaging: > 90% recycled materials

User manual: 100% recycled paper

Weight and dimensions

Dimensions of packaging (LxWxH): 595 x 400 x 352 mm

Dimensions of product (LxWxH): 506 x 310 x 317 mm

Weight of product: 6.2 kg

