

Philips  
Mini Audio System



FW-C330

## Rich Sound Experience

Set your sights on the attractive FWC330 Mini Hi-Fi System, which delivers superbly rich sound. You'll appreciate how easy it is to operate and control, just sit back, relax and enjoy your music all day, your way!

### **Enrich your sound experience**

- 2-Way Bass Reflex Speaker System for powerful sound
- 2 x 20W RMS/2 x 40W music power/ 800W PMPO

### **Continuous enjoyment of your favorite music**

- 3-disc changer for convenient multi-disc playback
- Dual Logic Tape Deck with auto replay

### **Personalized sound settings**

- Digital Sound Control for optimized music style settings
- 3-step Dynamic Bass Boost for deep bass experience

# PHILIPS

# Specifications

## Sound

- Output Power: 2 x 40W music power
- Sound Enhancement: Digital Sound Control, Dynamic Bass Boost 3 steps

## Loudspeakers

- Main Speaker: 2 way, Bass Reflex Speaker System, 5.25" woofer, Piezo tweeter

## Audio Playback

- Playback Media: CD, CD-R, CD-RW
- Loader Type: 3 CD Carousel
- Number of Discs: 3
- Disc Playback Modes: Repeat/one/all/program, Shuffle Play, 40-Track Programmable
- Cassette Deck Technology: Logic
- Cassette Playback Modes: Autoreverse, Electronic Speed Control, Full Auto Stop, Tape Counter

## Audio Recording

- Recording Media: Tape
- Tape Recording Enhancement: Automatic Recording Level, CD Synchro Start Recording, Timer for recording from tuner

## Tuner/Reception/Transmission

- Auto digital tuning
- Tuner Bands: FM Stereo, MW
- Tuner Enhancements: Auto Store, Easy Set (Plug &

Play)

- RDS: News, Program Type, Radio Text, RDS Clock Set, Station Name
- Station presets: 40

## Connectivity

- Headphone: 3.5 mm
- Other connections: FM Antenna, MW Antenna
- Aux in: Line in

## Convenience

- Alarms: CD Alarm, Radio Alarm, Sleep timer
- Clock: On main display
- Display Type: FTD
- Eco Power Standby: 1 watt

## Accessories

- Included accessories: AC Power Cord, FM/MW Antenna
- Remote control: 19-key

## Dimensions

- Set dimensions (W x H x D): 265 x 310 x 365 mm
- Main speaker dimensions (W x H x D): 210 x 310 x 235 mm
- Packaging dimensions (W x H x D): 619 x 410 x 474 mm
- Weight incl. Packaging: 11.6 kg

# Highlights

## 2-Way Bass Reflex System

2-Way Bass Reflex Speaker System for powerful sound

## 2x20W RMS/2x40W music power

2 x 20W RMS/2 x 40W music power/ 800W PMPO

## 3-disc changer

With a three-disc changer for music playback, you can choose between three different CDs inside the device at any one time. This convenient feature allows you to savor a variety of music while saving you precious time from changing CDs frequently.

## Dual Logic Tape Deck

Dual Logic Tape Deck with auto replay

## Digital Sound Control

Digital Sound Control offers you a choice of pre-set Jazz, Rock, Pop and Classic controls you can use to optimise the frequency ranges for different musical styles. Each mode uses graphic equalizing technology to automatically adjust the sound balance and enhance the most important sound frequencies in your chosen music style. Ultimately, Digital Sound Control makes it easy for you get the most out of your music by precisely adjusting the sound balance to match the type of music you are playing.

## 3-step Dynamic Bass Boost

Dynamic Bass Boost maximizes your music enjoyment by emphasizing the bass content of the music throughout the range of volume settings - from level one to level three - at the touch of a button! You can customize the bass level that fits your style. Bottom-end bass frequencies usually get lost when the volume is set at a low level. To counteract this, Dynamic Bass Boost can be switched on to boost bass levels, so you can enjoy consistent sound even when you turn down the volume.



Issue date 2014-02-05

Version: 3.0.4

12 NC: 9073 100 11232  
EAN: 87 10895 74240 5

© 2014 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)