

Mini Hi-Fi System

FW-C85

## 3 CD Changer Mini System with wOOx Technology

- 3000 watts PMPO
- 2 x 240 watts Music Power
- 2 x 120 watts RMS Stereo
- wOOx Technology
- Sound Navigation with jog shuttle
- 6 modes Digital Sound Control
- 6 modes Virtual Environment Control
- 6 Personal Settings
- 3-step wOOx level control
- Treble & Bass Control
- 7-band Spectrum Analyzer with 3 Display Modes
- 3-way Bass Reflex Speaker System with Detachable Grilles
- CD Text (/22 & /34)
- CD-Rewritable compatible
- Full RDS suite including 'NEWS' & Traffic Announcement (/22 & /34)
- Dolby B Noise Reduction (/22 & /34)
- Dual Logic Tape Deck with Auto Reverse (R+1)
- Digital Recording Ready (digital and line out)
- Subwoofer Ready
- Karaoke Feature (/21, /21M)
- Energy Saving Standby mode (<2 watts)



wOOx



Let's make things better.



PHILIPS

## 3 CD Changer Mini System with wOOx Technology

### standard product information

#### amplifier

- 3000 watts PMPO
- 2 x 240 watts Music Power
- 2 x 120 watts RMS,  $\pm 10\%$  THD, 6 Ohm, 1 kHz
- Sound Navigation : Jog Shuttle
- 6 modes Digital Sound Control
- 6 modes Virtual Environment Control
- 6 Personal Settings
- wOOx Dynamic Amplification Control
- 3-step wOOx level control
- Bass/Treble control
- Signal Dep Bass Control

#### compact disc player

- 3 CD changer
- CD-Rewritable compatible
- Digital servo technology
- Bit-check D/A converter
- 40-track CD Random Program
- Play modes (repeat/shuffle/program)
- CD (repeat track/disc/all)
- Change 2 discs while playing 1
- CD Text (/22 & /34)

#### tuner

- RDS: station name, program type, RDS text, clock set (/22 & /34)
- RDS: 'NEWS' & Traffic Announcement (/22 & /34)
- FM/MW/LW Digital Tuning with 40 presets (LW /22)
- Easy set/auto store for radio (and clock /22 & /34)

#### tape deck

- Dolby B Noise Reduction (/22 & /34)
- Dual Logic Tape Deck
- Auto Reverse (R+1)
- High and normal speed dubbing
- CD synchro recording
- Automatic recording level control
- Automatic tape type selection
- Electronic speed control and full auto stop
- Electronic tape counter

#### loudspeaker boxes

- 3-way Bass Reflex
- 6.5" woofer
- 2.5" Ferro Fluid Tweeter
- 2 x 1" polydome tweeter
- wOOx Technology
- 5.0" Top firing wOOx Bass Radiator
- Detachable grilles
- Click-fit connectors


#### connections

- Stereo headphones: 3.5mm stereo jack
- Video/Aux: cinch type sockets
- Subwoofer out: cinch type socket
- Digital Recording Ready:
  - digital out: cinch type socket
  - line out: cinch type socket
- Karaoke mic: 3.5mm jack (/21, /21M)

#### general

- 3 display modes incl. NITE mode
- Multicolor FTD display
- 7-band Spectrum Analyzer
- Demo mode
- Clock/timer
- 2 timer modes (wake-up/sleep)
- Wake-up with CD, tuner or tape
- 45-key Remote Control
- Automatic clock set via RDS (/22 & /34)
- Karaoke feature (/21, /21M)
- Energy Saving Standby mode (<2 watts) (/22 & /34)

	/21m	/21	/22	/30	/34
<b>Asia Pacific</b>	•	•			
<b>Australia/NZ</b>					
<b>Middle East/S Africa</b>	•				
<b>Latam</b>		•			
<b>Europe</b>			•		
<b>E Europe</b>					•
<b>Mexico</b>		•			
<b>tuner</b>					
FM87.5-108MHz	•	•	•	•	
MW522-1602kHz	•	•	•	•	
LW153-279kHz				•	
FM75 Ohm clickfit	•	•	•	•	
<b>mains supply</b>					
120/230V 50-60Hz	•	•			
230V/50Hz				•	•
<b>general</b>					
made in sticker			•	•	



EAN: 87 10101 63185 1 (/21)  
 EAN: 87 10101 63402 9 (/21M)  
 EAN: 87 10101 64053 2 (main unit) (/22)  
 EAN: 87 10101 64058 7 (L/R LSB) (/22)  
 EAN: 87 10101 63184 4 (/34)

Product Dimensions:  
 265mm W x 310mm H x 390mm D (main unit)  
 260mm W x 350mm H x 315mm D (speakers)

Package Dimensions:  
 594mm W x 720mm H x 416mm D (/21, /21M, /34)  
 356mm W x 410mm H x 474mm D (main unit) (/22)  
 408mm W x 708mm H x 310mm D (L/R LSB) (/22)

Product weight: 20 kg  
 Carton contains: CD Mini System, Multi-Function Remote Control, Batteries (2 x AA), Operating instructions, Warranty information, FM antenna, AM antenna

Printed in Singapore  
 Date printed : Nov 1999  
 Specifications subject to change without notice.

© 1999 Royal Philips Electronics N.V.  
 All rights reserved.

Dolby B NR System and the double-D symbol are trademarks of Dolby laboratories Licensing Corporation  
 Manufactured under license from Dolby Laboratories Licensing Corporation.

<http://www.philips.com>