

90+90
50+25+25
watts music power



**Mini Hi-Fi System with 3CD Changer,
 2 x 90 Watts, 50 + 25 + 25 Watts Music Power,
 Logic Deck & 5-speaker Dolby Pro-Logic System**

- 2 x 90 Watts, 50 + 25 + 25 Watts Music Power
- 2 x 45 Watts, 25 + 12.5 + 12.5 Watts RMS Stereo
- 5 Speaker Dolby Pro-Logic Speaker System
- Sound Navigation via Jog (6 Digital Sound Control & 6 Virtual Ambience Control)
- 3 steps Dynamic Bass Boost
- 3" Interactive Dashboard Display
- 2-way Bass Reflex Speaker System with Detachable Grilles
- Magnetically Shielded, Front and Center Speakers
- Plays CD, CD-R and CD-RW discs
- FM/MW/LW Digital Tuning with 40 presets
- Dual Logic Tape Deck with Auto Replay
- Bedroom Clock with Wake-up Alarm and Sleep-timer
- Subwoofer Ready
- 37-key Remote Control



Let's make things better.



PHILIPS



Mini Hi-Fi System with 3 CD Changer, 2 x 90 Watts, 50 + 25 + 25 Watts Music Power, Logic Deck & 5-speaker Dolby Pro-Logic System

standard product information

amplifier

- 2 x 90 watts, 50 + 25 + 25 watts Music Power
- 2 x 45 watts, 25 + 12.5 + 12.5 watts RMS, ±10%THD, 6 Ohm, 1 kHz
- 5-Speaker Dolby® Pro-Logic System
- Sound Navigation via Jog
 - 6 Digital Sound Control (Digital, POP, Classic, Rock, New Age, Electric)
 - 6 Virtual Ambience Control (Hall, Cinema, Arcade, Concert, Disc, Cyber)
- 3 Dynamic Bass Boost
 - Beat, Punch, Blast

compact disc player

- 3 CD Changer
- Plays CD, CD-R and CD-RW discs
- Digital servo technology
- Bit-check D/A converter
- 40-Track CD Random Program
- Play modes (repeat/shuffle/program)
- Change 2 discs while playing 1

tuner

- RDS : station name, program type, RDS text, clock set
- RDS : 'NEWS' & Traffic Announcement
- FM/AM Digital Tuning with 40 presets
- Plug & Play for easy installation of radio stations

tape deck

- Dual Logic Tape Deck
- Auto Replay
- Normal speed dubbing
- CD Synchro recording
- Automatic recording level control
- Automatic tape type selection
- Electronic speed control and full auto stop

loudspeaker boxes

- 2-way Bass Reflex Speaker
- 5 1/4" woofer
- 2" Ferro Fluid Tweeter
- Magnetically Shielded (front & center speakers)
- 6 Ohm
- Detachable cloth grilles

surround speaker

- 3" full range surround speaker
- 3 Ohm

center speaker

- 3" full range center speaker
- 6 Ohm
- Magnetically shielded


connections

- Stereo headphones : 3.5mm stereo jack
- CDR/DVD-Aux/TV-Aux : cinch type socket
- Subwoofer-out : cinch type socket
- Color coded cables :
 - Front : red/black
 - Center : blue/black
 - Surround : grey/white

general

- 3 Display modes include Dim mode
- Interactive Dashboard Display with VU meter
- Demo mode
- Clock / Timer
- 2 timer modes (wake-up/sleep)
- 37-key remote control
- Automatic clock set via RDS

	/21	/21M	/22	/30	/33	/34
Asia Pacific						
Australia/NZ						
Middle East/S Africa						
Latam						
Europe				•		
E Europe						•
Mexico						
Korea						
tuner						
FM87.5-108MHz				•		•
MW522-1602kHz				•		•
LW153-279kHz				•		
FM75 Ohm coaxial				•		•
mains supply						
120/230V 50-60Hz						
230V/50Hz				•		•
220V/60Hz						
general						
made in sticker						•



EAN: 87 10895 70301 7 (/22)
EAN: 87 10895 70302 4 (/34)

Product Dimensions:
265 mm W x 310 mm H x 390 mm D (center unit)
240 mm W x 310 mm H x 315 mm D (speakers)
260 mm W x 115 mm H x 240 mm D (center speaker)
178 mm W x 90 mm H x 178 mm D (surround speaker)

Package Dimensions:
772 mm W x 410 mm H x 474 mm D
Product weight: 18 kg
Carton contains: CD Mini System, Surround Sound Speakers, Multi-Function Remote Control, Batteries (2 x AA), Operating instructions, Warranty information, FM antenna, AM antenna

Printed in Singapore
Date Printed : Feb 2001 (Version 1)
Specifications subject to change without notice.
© 2000 Royal Philips Electronics N.V.
All rights reserved.

<http://www.philips.com>

Let's make things better.



PHILIPS