

CDR Mini System

FW-R7

## Mini Hi-Fi System with Integrated CD-Recorder

- 2 x 100 watts Music Power
- 2 x 50 watts RMS
- Make your own CDs with Integrated CD-Recorder
- 3 CD Changer
- Double speed recording from CD
- CD Text input, editing and recording
- Simplified recording modes : CD > CD and Compile CD
- Record onto CD from CD changer, radio or any external source
- Automatic Level Control for perfect compilations with the same volume level
- Digital Sound Control (6 settings) with Loudness on/off
- 3-way Bass Reflex Speaker System
- Subwoofer ready
- Digital and line input and output
- 42-key Remote Control



Let's make things better.



PHILIPS

# Mini Hi-Fi System with Integrated CD-Recorder

## standard product information

### amplifier

- 2 x 100 watts Music Power
- 2 x 50 watts RMS,  $\pm 10\%$  THD, 6 $\Omega$ m, 1kHz
- Digital Sound Control (6 settings)
- Incredible Surround™
- Loudness and Pure on/off
- Balance Left/Right (via remote control)

### compact disc recorder

- Records on all Digital Audio CD-R and CD-RW discs
- Double speed recording and finalising from CD changer
- CD Text input, edit and record
- Automatic Level Control ensures constant playback volume of compilation CDs
- Direct Line Recording for bit-perfect recording from CD changer
- Play modes (repeat/shuffle/program)
- CD-Rewritable compatible

### compact disc changer

- CD Text
- Motorized front loading 3 CD changer
- CD-Rewritable compatible
- Track (A-B) editing mode
- Play modes (repeat/shuffle/program)
- Change 2 discs while playing 1
- Plays unfinalized CD-R and CD-RW discs

### tuner

- FM/MW/LW digital tuner with 40 presets
- Full RDS suite with News! and traffic announcement (/22 only)
- Easy Set/auto store for radio and clock

### loudspeaker boxes

- 3-way Bass Reflex System
- 6.5" Woofer
- 2.5" Ferro Fluid cooled Tweeter
- 1" polydome tweeter
- detachable speaker cloth
- click-fit connectors


### connections

- Digital input with sample rate converter (12-56 kHz) : cinch type socket
- Digital output (44.1 kHz) : cinch type socket
- Line input and output : cinch type sockets
- Subwoofer output : cinch type sockets
- Stereo headphone output : 3.5 mm stereo jack

### general

- Large multi colour FTD display with dot-matrix text and music calendar
- 7 band spectrum analyzer
- Display dimming in 3 steps (via remote control)
- Demo mode and dealer tray blocking mode
- Clock with record/wake-up/sleep timer
- 42-key remote control
- Energy Saving standby mode (<2 watts, not for /21)

	/21	/22	/33
Asia Pacific	•	•	•
Australia/NZ		•	
E Europe		•	
Europe		•	
Korea			•
Latam			
Mexico			
Middle East/S Africa	•		
<b>tuner</b>			
FM-87.5-108MHz	•	•	•
MW531-1602kHz	•	•	•
LW153-279kHz		•	•
RDS-News!-TA		•	
FM750 Ohm coaxial	•	•	•
<b>mains supply</b>			
120/240V 50Hz	•		
230V/50Hz		•	•



EAN: 87 10101 63189 9 (/21)  
 EAN: 87 10101 63188 2 (/22)  
 EAN: 87 10101 63375 6 (/33)

Product Dimensions:  
 265mm W x 310mm H x 335mm D (center unit)  
 240mm W x 310mm H x 250mm D (speakers)

Package Dimensions:  
 580mm W x 719mm H x 358mm D

Product weight: approx. 2.2 kg

Carton contains: CDR Mini System, Multi-Function Remote Control, Batteries (2 x AA), Operating Instructions, Warranty information, FM antenna, AM antenna

Printed in Singapore

Date printed: Nov 1999

Specifications subject to change without notice.

© 1999 Royal Philips Electronics N.V.

All rights reserved.

Incredible Surround™ is a Trademark of Philips Consumer Electronics Company

In some countries, use of the CDR Mini Hi-Fi System as shown or suggested in this leaflet may require the authorization of copyright holders.

<http://www.philips.com>