

CD CHANGER MINI SYSTEM

FW 355C



CD CHANGER MINI SYSTEM

- **1000W PMPO** Plenty of power for a great room- filling sound
- **2 X 50W RMS** Plenty of power for a great room- filling sound
- **3-Disc Changer** Over 3.6 hours of continuous music enjoyment
- **Incredible Surround** Hear big-system performance with sensational concert-hall effect
- **RDS Radio Data System** Keeps you instantly informed about stations and programmes(Europe only)
- **20 Preset Stations Tuner** Digital tuner with 20 preset stations
- **DBB** Dynamic bass boost enhance the low tone
- **DSC Digital Sound Control** Match the sound to the preset graph equalizer
- **2-Way Loudspeakers** Compact speakers with great sound and great styling
- **Low Consumption on Stand-by Mode** Environmental friendly (Europe only)



Let's make things better.



PHILIPS

Standard product information

COMPACT DISC PLAYER

- 3 Disc Changer
- Programmable memory for 40 tracks
- Program review facility
- Shuffle enables random playing of tracks
- Next and previous keys for track skip
- Frequency range 20 - 20000 Hz
- Signal-to-noise ratio 90 dB
- Digital Servo Control Mechanism
- CD changer lens
- Time mode

CASSETTE DECK

- Dual stereo decks(Playback and recording/playback)
- High and normal speed dubbing
- Automatic recording level control
- Automatic tape type selection
- Electronic speed control

TUNER

- PLL quartz digital tuner
- 20 random presets
- Up/down single step and search tuning
- Automatic programming of tuner presets
- Wave band selector
- FM antenna wire

AMPLIFIER

- 2 x 50W RMS, 6 ohm, +/-10% THD
- 1000W PMPO
- 2 x 100W Music Power Output
- Dynamic bass boost
- Incredible surround
- CD, tape, tuner and aux sources
- Digital sound control (Jazz, Classic, Rock, Pop and Optimal)
- Visual sound icons

TIMER

- Precision quartz controlled clock
- Automatic clock set via RDS(Europe only)
- Wake up with CD or Tuner

LOUDSPEAKER BOXES

- 2-Way bass reflex
- 5.25" woofer
- 2.5" tweeter
- Dimensions (mm) (w x h x d) : 200 x 310 x 226

CONNECTIONS

- Stereo headphones : 3.5 mm stereo jack
- Video/Aux : cinch type sockets
- Loudspeaker : clipfit connections
- Matrix surround output : clipfit connections(USA only)
- Sub-woofer output : cinch type socket

GENERAL

- Monoblock configuration
- 23 key remote control
- Trade mode via "DEMO" button
- Dimensions with LSB L/R (mm) (w x h x d) : 665 x 310 x 360
- Backlit keys

	/21m	/21	/22	/22S	/37	/25	/34	/30
Asia Pacific		•						•
Europe			•	•		•		
Overseas		•						
USA					•			
Tuner								
FM 65.81 – 74 MHz								
FM 87.5 – 108 MHz	•	•	•	•	•	•	•	•
MW 522 – 1602 kHz	•	•	•	•	•	•	•	•
FM 75 ohm coax input	•	•	•		•			•
FM 300 ohm clickfit				•				
RDS with clock set			•	•		•		
Karaoke								
Mic Mixing		•						•
*/30 with different type of loudspeakers boxes								

	/21m	/21	/22	/22S	/37	/25	/34	/30
Asia Pacific		•						•
Europe			•	•		•		
Overseas		•						
USA					•			
Mains Supply								
230V / 50 Hz			•	•		•		
120/230V / 50/60 Hz	•							•
120V/60 Hz				•				
General								
Made In Sticker	•	•	•	•	•	•	•	•
Silver Version				•				

