

DOLBY PROLOGIC CD CHANGER MINI SYSTEM

FW 375P



DOLBY PROLOGIC CD CHANGER MINI SYSTEM

- **Dolby Surround Prologic** Exciting Home Cinema
- **3-Disc Changer** Over 3.6 hours of continuous music enjoyment
- **1200 W PMPO** Plenty of power for a great room- filling sound
- **2 X 40W, 20W, 20W RMS** Plenty of power for a great room- filling sound
- **2 X 80W, 40W, 40W Music Power** Plenty of power for a great room- filling sound
- **Incredible Surround** Hear big-system performance with sensational concert-hall effect(except USA)
- **20 Preset Stations Tuner** Digital tuner with 20 preset stations
- **DBB** Dynamic bass boost enhance the low tone
- **DSC Digital Sound Control** Match the sound to the preset graph equalizer
- **3-Way Loudspeakers** Compact speakers with great sound and great styling
- **Dolby Surround Prologic Loudspeaker set(FB203) Included**
Total solution for Dolby Surround Prologic



Let's make things better.



PHILIPS

Standard product information

COMPACT DISC PLAYER

- 3 Disc Changer
- Programmable memory for 40 tracks
- Program Review facility
- Shuffle enables random playing of tracks
- Next and previous keys for track skip
- Frequency range 20 - 20000 Hz
- Signal-to-noise ratio 90 dB
- Digital Servo Control Mechanism
- CD Changer lens
- Time mode

CASSETTE DECK

- Dual stereo decks(Playback and recording/playback)
- High and normal speed dubbing
- Automatic recording level control
- Automatic tape type selection
- Electronic speed control

TUNER

- PLL quartz digital tuner
- 20 random presets
- Up/down single step and search tuning
- Automatic programming of tuner presets
- Wave band selector
- FM antenna wire

AMPLIFIER

- 2 x 40W RMS, 6 ohm, +/-10% THD (Stereo Mode)
- 2 x 40W + 20W + 20W RMS, 6 ohm, 1kHz, +/-10% THD (Dolby Prologic Mode)
- 1200W PMPO (Total Output)
- 2 x 80W + 40W + 40W Music Power Output
- Dynamic bass boost
- Incredible surround(except USA)
- CD, tape, tuner and aux sources
- Digital Sound Control (Jazz, Classic, Rock, Pop and Optimal)
- Visual Sound Icon

TIMER

- Precision quartz controlled clock
- Wake up with CD or Tuner
- Record timer

LOUDSPEAKER BOXES

- Front Left/Right
- 3-Way bass reflex shielded
 - 5.25" woofer
 - 2.5" tweeter
 - 1" PolyDome tweeter
 - Dimensions (mm) (w x h x d) : 200 x 310 x 226

Center

- 2 Way shielded, closed type
 - 2 x 4" woofer
 - 1" PolyDome tweeter
 - Dimensions(mm) (w x h x d) : 400 x 152 x 160
- Surround
- Full range closed type
 - 3" full range speaker
 - Dimensions(mm) (w x h x d) : 135 x 190 x 90

CONNECTIONS

- Stereo headphones : 3.5 mm stereo jack
- Video/Aux : cinch type sockets
- Loudspeaker : colour guiding click-fit connectors
 red/black : for left and right
 blue/black : for center
 white/black : for surround
- Sub-woofer output : cinch type socket

GENERAL

- Monoblock configuration
- 26 key remote control
- Trade mode via "DEMO" button
- Dimensions with LSB L/R (mm) (w x h x d) : 665 x 310 x 360
- Backlit keys

	/21m	/21	/22	/37	/25	/34	/30	/33	/26	/41		/21m	/21	/22	/37	/25	/34	/30	/33	/26	/41		
Asia Pacific		•					•					Asia Pacific		•				•					
Europe												Europe											
Overseas												Overseas											
USA				•								USA			•								
Tuner																							
FM 65.81 – 74 MHz																							
FM 87.5 – 108 MHz		•		•			•					120/230V / 50/60 Hz		•									
MW 522 – 1602 kHz		•		•			•					120V/60Hz			•								
FM 75 ohm coax input		•					•					General											
FM 300 ohm clickfit				•								Made In Sticker		•		•			•				
Karaoke																							
Mic Mixing		•					•																

