

CD Mini System

FW570C

3-Disc CD Changer with 200 Watts Total Power Incredible Surround™ and Auto Reverse

- 2 x 100 Watts RMS Stereo
- Incredible Surround™
- G-Sound Technology
- Dual Full Logic Tape Deck
- Auto Reverse
- Digital Sound Control (Optimal, Jazz, Rock, Techno, Classic)
- 3-Step Dynamic Bass Boost
- Subwoofer Ready
- 40-Track CD Programmability
- AM/FM Stereo Digital Tuner with 40 Presets
- Oversized, MultiColor, Digital FTD Display
- 24-Button Remote Control
- 3-Way Speaker System with Bass Reflex and Removable Grilles
- One Touch CD Synchro Recording
- Bedroom Clock with Wake-up Alarm



3 CD CHANGER

200watts
Total Power



Incredible
Surround

auto reverse



EASY RADIO SET



Let's make things better.

PHILIPS MAGNAVOX

CD Mini System FW570C

Sound Enhancement

2 x 100 Watts RMS Stereo

100 watts continuous RMS power output per channel, at 6 Ohms, from 80Hz-16kHz, with no more than 10% Total Harmonic Distortion (THD).

G-Sound Technology

Ultra-efficient Super Class G amplifier with Gyros switching for overload protection offers unadulterated, relentless music quality at any volume level. Ferro-fluid cooled tweeter and Polydome tweeter for crisp high tones.

Incredible Surround™

An exciting, new, psycho-acoustic method of widening the stereo spatial image especially suited for applications with limited separation of left and right speakers.

Digital Sound Control

(Optimal, Jazz, Rock, Techno, Classic)

Digital sound control (or DSC) offers different sound settings tailored for specific musical styles.

3-Step Dynamic Bass Boost (Beat, Punch, Blast)

Bass reproduction is essential for deep and rich music. 3 Step DBB offers the optimal level for any kind of music.

3-Way Speaker System with Bass Reflex

Equipped with one 6 1/2" G-Cone woofer for smooth low and mid range reproduction, one 2 1/2" ferro-fluid cooled tweeter and two 1" Polydome tweeters for crisp high tones.

AM/FM Stereo Digital Tuner


State-of-the-art precision tuning system insures precise, accurate station selection every time, along with the greatest performance and reliability available.

Subwoofer Ready

Affords easy access to greater dimensions in sound with output signals available for connection to a subwoofer.

Bitcheck Digital-to-Analog Conversion

Employs dynamic element matching to eliminate deviations in bit current to eliminate crossover distortion and supply extremely high linearity in audio reproduction.



Convenience

3-CD Changer with Motorized Drawer

Multi-disc play capability provides more than three hours of continuous music.

Dual Full Logic Tape Deck

Offer the ability to switch from one function, such as fast forward, to another function, such as play, by remote control.

Auto Reverse

The feature employs an auto reverse mechanism to sense the end of the tape and automatically reverse the direction of tape travel in the PLAY mode providing an uninterrupted, continuous flow of music without manually flipping the cassette tape.

24-Button Remote Control

This infrared remote control operates volume +/-, all CD functions (POWER, NEXT, PREVIOUS, PLAY, STOP, PAUSE, REPEAT, SHUFFLE, PROGRAM, DISC 1, 2, 3), CD, AUX, TAPE 1/2, TUNER, SIDE and sound enhancement features including Incredible Surround™, Dynamic Bass Boost, and Digital Sound Control.

Easy Set

Press Standby 'ON' for 2 secs to automatically program 40 tuner presets. (FM only)

40-Random Channel Presets

Random memory presets allow pre-programming of up to 40 AM and FM station frequencies into the tuner memory.

Auto Store

Automatically stores up to 40 preset FM or AM stations.

40-Track CD Programmability

Store up to 40 of your favorite CD track selections, from one or multiple discs, to be played back in the order in which they are programmed anytime you like.

Auto Record Level Control

Micro electronic circuitry constantly monitors the final audio amplifier stage to insure accurate, distortion-free recordings every time.

Video/AUX Input

For connection of audio accessory pieces such as a LD or DVD player, television, or external cassette deck.

Auto Source Selection

Automatically switch to a new source and pause the current source at the touch of a single button.

Demo Mode

Functions always. Press "STOP" for 3 secs to interrupt demo mode.

Direct Play Button

Allows you to select and play any CD in the carousel by touching only one button.

Change While Play

Flexibility of changing 2 discs while still listening to the third disc being played.

One-Touch CD Synchro Recording

One button allows the cassette deck and CD player to communicate with one another to synchronize the start of a recording on an analog audio cassette deck with the start of a CD or a CD program.

Repeat

Repeat your favorite track.

Pause

Interrupts playback of a CD without returning to the beginning of the disc, so when play resumes, the music begins exactly where it stopped.

Shuffle One/All Discs

Plays all selections on a particular disc or multiple discs in multi-disc players in random order, ignoring the sequential order in which they were originally recorded.

Next/Previous Skip

This two button feature offers you the opportunity to skip back to the previous track or skip up to the next track instantly.

High-Speed Dubbing/Continuous Play

High-speed dubbing makes it possible to create good quality recordings (dubs) from one tape to another at twice the normal speed in RECORD mode. Continuous play offers automatic switching from cassette deck A to cassette deck B providing an uninterrupted, continuous flow of music in the PLAY mode.

Clock/Timer

Set the alarm portion of a built-in digital clock to wake you to music from your favorite CD or an AM/FM radio station at any desired time of the day.

Stereo Headphone Jack

Design

Design Concept

The linear theme, and contrasting surface definitions, reflecting future "edge design" trends, combine to create a modern and attractive design. Attention to details, interactive lighting, and the use of rich materials and metallic finishings further compliment the visual appeal. The element of power is visualised through the dramatic three dimensional speaker box surfacing.

Oversized, MultiColor, Digital FTD Display

This large display is easy to read at any distance with no distortion or distraction and the multi-color format makes it easy to recognize different functions at a glance.

PIINGS (Philips Magnavox Intelligent Navigation Guidance System)

Onboard intelligence monitors the systems and provides information on status and available functions by means of backlighting.

Ergonomic Control Layout

Convenient grouping of related functions along with positive tactile feedback from front-mounted controls optimize this model for comfort and convenience.

Removable Cloth Speaker Grilles

UPC Code: 037849863633

Product Dimensions:

10.5"W x 12.4"H x 12.2"D (electronics)

10.2"W x 12.8"H x 12.2"D (speakers)

Package Dimensions:

24"W x 29"H x 16"D

Product weight: 42 lbs.

Carton contains: CD Mini System, Multi-Function Remote Control, Batteries, Operating instructions, Warranty information

Printed in Singapore

©1997 Philips Consumer Electronics Co.

A Division of Philips Electronics North America Corp.

Specifications subject to change without notice.

Incredible Surround™ is a Trademark of Philips Consumer Electronics Company

Let's make things better.

PHILIPS MAGNAVOX