

## CD CHANGER MINI SYSTEM

**FW 750C**



## CD CHANGER MINI SYSTEM

- **2 x 100W RMS (USA)**
- **2 x 80W RMS or 2 x 160W music power (Europe)**
- **2 x 120W RMS (Overseas/ Asia Pacific)** Lots of power for a great room filling sound
- **2000 Watts PMPO**
- **Hydraulic Zoom Volume Control** Touch Me.....(limited versions)
- **Wireless Prepared** Prepared to connect to wireless stereo speakers system
- **Incredible Surround** Enhances stereo image by creating the impression that the loudspeakers are further part than they are
- **Double Full Logic Tape Deck** All functions via remote control
- **Single Auto Reverse Deck** Play and record with any reverse mode
- **Dolby B noise reduction** Only for Europe
- **Full RDS suite** Station name, programme type, RDS text, clock set (Europe only)
- **4-Way Side firing Loudspeakers with removable cloth** With great sound and great styling
- **3 Bass Ports** For powerful bass reproduction
- **Ferro fluid cooled tweeters** Decreases coloration and provides more sound stage
- **Flat Cone Speaker Technology** First mini system in the world. For solid and crisp sound
- **Magic Menu** Unique user interface simplifying usage of the set "what you see is what you need"
- **Optional** : Wireless active subwoofer FB 201 W or Wireless travelling sound unit FB 200 W
- **Save energy** : < 2W in standby mode (other comparable models 15W and higher ) Europe only



**HIGH  
POWER**



*Let's make things better.*



**PHILIPS**

# FW 750C

# CD CHANGER MINI SYSTEM

## Standard product information

### COMPACT DISC PLAYER

- 3 Disc Changer
- Programmable memory for 40 tracks
- Program Review facility
- Shuffle enables random playing of tracks
- Next and previous keys for track skip
- Frequency range 20 - 20000 Hz
- Signal-to-noise ratio 90 dB

### CASSETTE DECK

- Dual full logic decks(Playback and recording/play)
- Deck 2 full auto reverse
- High and normal speed dubbing
- CD synchro recording
- Continuous play
- Automatic recording level control
- Electronic speed control and full automatic stop
- Chrome (type II) and normal (type 1) tape recording

### TUNER

- RDS - station name, programme type, RDS text, clock set (only Europe)
- PLL quartz digital tuner
- 20 random presets
- Automatic programming of tuner presets

- Automatic FM Stereo/Mono switch and FM stereo broadcasting information
- Wave band selector

### AMPLIFIER

- 2 x 100W RMS, 6ohm, 1kHz, ±10% THD (for USA only)
- 2 x 80W RMS, 6 ohm, 1kHz, ±10% THD (for Europe only) or 2 x 160W music power (Overseas, Asia Pacific)
- 2000 Watts PMPO
- Hydraulic Zoom Volume Control (limited versions)
- Incredible Surround (3 steps)
- Dynamic bass boost (3 steps)
- Digital Sound Control (Jazz, Classic, Rock, Pop or Techno and Optimal )

### TIMER

- Precision quartz controlled clock
- Automatic clock set via RDS(Europe only)
- Wake up with CD, Tuner or Tape

### LOUDSPEAKER BOXES

- Side firing tweeters
- 4-Way bass reflex

- 3 Bass Ports
- 1 x 5.25" flat cone woofer
- 1 x 2.5" ferro fluid cooled tweeter
- 2 x 1" PolyDome tweeter
- Dimensions (mm) (w x h x d) : 240 x 310 x 230
- Click-fit connectors
- Removable cloth

### CONNECTIONS

- Wireless Prepared : cinch type line out for wireless active subwoofer or wireless travelling sound unit or wireless stereo speaker system
- Stereo headphones : 3.5 mm stereo jack
- DVD/Aux : cinch type sockets
- Sub-woofer output : cinch type socket for active subwoofer (eg FB201)

### GENERAL

- 26-key Audio/Video remote control
- Auto Demo mode
- Display dimmer via remote control
- Dimensions with LSB, L/R (mm) (w x h x d) : 745 x 310 x 250
- Backlit keys for 3 CD direct play, 4 sources keys, Incredible Surround and Dynamic Bass Boost

	/21S/22S	/22	/37	/25	/34S/30S/33S/41S		/21S/22S	/22	/37	/25	/34S/30S/33S/41S
<b>Asia Pacific</b>	•	•	•	•	•	•	•	•	•	•	•
<b>Europe</b>		•	•		•			•	•		•
<b>Overseas</b>	•				•						•
<b>USA</b>				•							
<b>Tuner</b>											
FM 65.81 – 74 MHz					•						
FM 87.5 – 108 MHz	•	•	•	•	•	•	•	•	•	•	•
MW 522 – 1602 kHz	•	•	•	•	•	•	•	•	•	•	•
FM 75 ohm coax input	•	•	•		•	•	•	•	•	•	•
FM 300 ohm clickfit				•							
RDS with clock set		•	•		•	•					
<b>Sound</b>											
Dolby NR		•	•		•	•					
<b>Karaoke</b>											
Dual Mic, Vocal fader											•
Digital echo											•
<b>Mains Supply</b>											
120V / 60 Hz									•		
230V / 50 Hz			•	•		•	•			•	•
120/230V / 50/60 Hz	•										•
<b>General</b>											
Made In Sticker	•	•	•	•	•	•	•	•	•	•	•
Black/Silver			•	•	•						
Silver/Grey	•	•				•	•	•	•	•	•
Hydraulic volume knob	•									•	•

