

CD Mini System

FW765P

Dolby® Pro Logic 3 CD Changer Mini System

- 2 x 80 watts + 40 watts + 2 x 20 watts music power
- 2 x 40 watts + 20 watts + 2 x 10 watts RMS Stereo
- 5 Speaker Dolby® Pro Logic Surround Sound System
- Incredible Surround™
- Dual full logic tape deck
- Auto reverse (R+1)
- Digital sound control (Optimal, Jazz, Rock, Techno, Classic)
- 3-step dynamic bass boost (Beat, Punch, Blast)
- Subwoofer ready
- 40 track CD programmability
- FM/MW/LW* stereo digital tuner with 40 presets (* -/22 only)
- Full RDS suite including "NEWS"
- 3 way bass reflex speaker system with detachable grilles
- Easy set for tuner and clock
- Bedroom clock with wake up alarm
- Wireless prepared

2x80+40+2x20
wattsMPO



Let's make things better.



PHILIPS

Dolby® Pro Logic 3 CD changer mini system

standard product information

amplifier

- 2 x 80 watts + 40 watts + 2 x 20 watts music power
- 2 x 40 watts + 20 watts + 2 x 10 watts RMS, ±10% THD, 6 ohm, 1 kHz
- 5 Speaker Dolby® Pro Logic Surround Sound System
- Incredible Surround™
- digital sound control (optimal, jazz, rock, techno, classic)
- 3-step dynamic bass boost (beat, punch, blast)
- signal attenuated bass control

compact disc player

- motorized front loading 3 CD changer
- digital servo technology
- bit-check D/A converter
- 40 track CD random program
- play mode (repeat/shuffle/program)
- change 2 discs while play 1

tuner

- RDS - station name, programme type, RDS text, clock set
- RDS - "NEWS" feature
- FM/MW/LW* stereo digital tuner with 40 presets (* /22 only)
- 40 preset memory station in FM/MW band
- easy set/auto store for tuner and clock

tape deck

- dual full logic tape deck
- auto reverse (R+1)
- high speed dubbing
- CD synchro recording
- continuous play
- automatic recording level control
- automatic tape type selection
- electronic speed control and full auto stop

optional accessories :



FB201 Active Subwoofer



FB202W Wireless Active Subwoofer

loudspeaker boxes

- 3 way bass reflex
- 6.5" G cone woofer
- 2.5" gradually cooled ferro fluid tweeter
- 1" polydome tweeter
- magnetically shielded
- detachable grilles
- hyper energy bass ports for deep powerful bass reproduction

surround speaker

- 1 way speaker (3" full range)
- 6 Ohm

center speaker

- 1 way speaker (4" full range)
- 12 Ohm
- magnetically shielded

connections

- stereo headphones : 3.5mm stereo jack
- video/aux : cinch type sockets
- subwoofer output (see optional accessories)
- line out - wireless prepared (see optional accessories)
- surround : click fit and cinch type


general

- fluorescent tube display
- clock/timer
- wake up with CD, tuner or tape
- 32-key remote control
- PINGS (Philips Intelligent Navigation Guidance System) for ease of operation
- automatic clock set via RDS

	/22	/34
Europe	•	•
E Europe	•	•
tuner		
FM65.81-74MHz	•	•
FM87.5-108MHz	•	•
MW522-1602kHz	•	•
LW153-279kHz	•	•
FM75 ohm clickfit	•	•
RDS	•	•
mains supply		
230V/50Hz	•	•
general		
made in sticker	•	•

5 Speaker Surround Sound System

Philips 5 Speaker Dolby® Pro Logic Surround Sound System treats homeviewers to cinema sound quality that has until now, remained in the realm of cinemas. Simply connect to hifi VCR or stereo TV.



Product Dimensions:
267mmW x 310mmH x 310mmD (electronics)
240mmW x 310mmH x 305mmD (speakers)
200mmW x 98mmH x 98mmD (surround)
264mmW x 140mmH x 240mmD (center)
Package Dimensions:
777mmW x 410mmH x 654mmD
Product weight: 23 kg
Carton contains: CD Mini System, Surround Sound Speakers and Center Speaker, Multi-Function Remote Control, Batteries, Operating instructions, Warranty information, FM antenna, AM antenna

Printed in Singapore
Specifications subject to change without notice.
Incredible Surround™ is a Trademark of Philips Consumer Electronics Company
Dolby® Pro Logic is a trademark of Dolby Laboratories

