

CD Mini System

FW870C

## 3 CD Changer Mini System with Interactive Sound Studio

- 2800 watts PMPO
- 2 x 260 watts Music Power
- 2 x 130 watts RMS Stereo
- G-Sound Technology
- Interactive Sound Studio
- 9-band Spectrum Analyzer with 5 Display Modes
- 3-way Bass Reflex Speaker System with Detachable Grilles
- Super Large Woofer
- CD Text (1/22 & 1/34)
- CD-Rewritable compatible
- Full RDS suite including 'NEWS' & Traffic Announcement (1/22 & 1/34)
- Dolby B Noise Reduction (1/22 & 1/34)
- Dual Logic Tape Deck with Auto Reverse (R+1)
- Digital Recording Ready (digital and line out)
- Subwoofer Ready
- Karaoke Feature
- Energy Saving Standby mode (<2 watts) (1/22 & 1/34)

**3 CD** **260 WATT MUSIC POWER**  
**2800** watts PMPO **2x260** watts MPO



Let's make things better.



PHILIPS

# CD Mini System FW870C

## 3 CD Changer Mini System with Interactive Sound Studio

### standard product information

#### amplifier

- 2800 watts PMPO
- 2 x 260 watts Music Power
- 2 x 130 watts RMS,  $\pm$  10% THD, 6 Ohm, 1 kHz
- G-Sound Technology:
  - Super Large Woofer
  - Super Class G Amplifier
  - Gyros switching
  - G-Bass port
  - G-cone
  - Ferro Fluid Tweeter
- Interactive Sound Studio:
  - 26 modes Digital Sound Control
  - Automatic Digital Sound Control
  - Calibration
  - 26 modes Virtual Environment Control (hall, disco, concert, cinema, club, arcade)
  - 4 Studio Effects (surf, 3D pan, hold, strobe) + MAX
  - 6 personal settings
- 3-step Dynamic Bass Boost (Beat, Punch, Blast)
- Bass Optimization

#### compact disc player

- CD Text (/22 & /34)
- motorized front loading 3 CD changer
- CD-Rewritable compatible
- digital servo technology
- bit-check D/A converter
- 40-track CD Random Program
- play modes (repeat/shuffle/program)
- repeat track/disc/all
- change 2 discs while playing 1

#### tuner

- RDS: station name, program type, RDS text, clock set (/22 & /34)
- RDS: 'NEWS' & Traffic Announcement (/22 & /34)
- FM/MW/LW Digital Tuner with 40 presets (LW /22)
- easy set/auto store for radio (and clock /22 & /34)

#### tape deck

- Dolby B Noise Reduction (/22 & /34)
- Dual Logic Tape Deck
- Auto Reverse (R+1)
- high and normal speed dubbing
- CD synchro recording
- automatic recording level control
- automatic tape type selection
- electronic speed control and full auto stop
- electronic tape counter

#### loudspeaker boxes


- 3-way Bass Reflex
- 8" woofer
- 2.5" Ferro Fluid Tweeter
- 2 x 1" polydome tweeter
- detachable grilles
- G-Bass Port in rear side
- click-fit connectors

#### connections

- stereo headphones: 3.5mm stereo jack
- video/aux: cinch type sockets
- subwoofer out: cinch type socket
- Digital Recording Ready:
  - digital out: cinch type socket
  - line out: cinch type socket
- Karaoke mic: 3.5mm jack

#### general

- 5 display modes incl. NITE mode
- multicolor FTD display
- 9-band Spectrum Analyzer
- music calendar
- demo mode
- clock/timer
- 2 timer modes (wake-up/sleep)
- wake-up with CD, tuner or tape
- 24-key Remote Control
- automatic clock set via RDS (/22 & /34)
- Karaoke feature
- Energy Saving Standby mode (<2 watts) (/22 & /34)



	/21m	/21	/22	/30	/34
Asia Pacific					
Australia/NZ					
Middle East/S Africa					
Latam			•		
Europe				•	
E Europe					•
Mexico			•		
<b>tuner</b>					
FM65.81-74MHz					(•)
FM87.5-108MHz			•	•	•
MW522-1602kHz			•	•	•
LW153-279kHz					•
FM75 Ohm clickfit			•	•	•
<b>mains supply</b>					
120/230V 50-60Hz				•	
230V/50Hz				•	•
<b>general</b>					
made in sticker				•	•

#### Interactive Sound Studio (ISS)

Interactive Sound Studio lets you create studio effects and personalized sound settings. Adjust the set to your type of music with the 26 modes of Digital Sound Control and, set the system to suit your environment through Virtual Environment Control.



EAN: 87 10101 35799 7 (/34)  
 EAN: 87 10101 35798 0 (/22)  
 EAN: 87 10101 35796 6 (/21)

Product Dimensions:  
 265mm W x 310mm H x 363mm D (center unit)  
 260mm W x 338mm H x 315mm D (speakers)

Package Dimensions:  
 594mm W x 720mm H x 398mm D

Product weight: 20 kg  
 Carton contains: CD Mini System, Multi-Function Remote Control, Batteries (2 x AA), Operating Instructions, Warranty information, FM antenna, AM antenna

Printed in Singapore  
 Date printed: Sept 1998  
 Specifications subject to change without notice.  
 © 1998 Koninklijke Philips Electronics N.V.

All rights reserved.  
 Dolby B NR System and the double-D symbol are trademarks of Dolby laboratories Licensing Corporation  
 Manufactured under license from Dolby Laboratories Licensing Corporation.

<http://www.philips.com>

Let's make things better.



**PHILIPS**