

240W

total power



Mini Hi-Fi System with 3CD Changer, 240 watts Total Power, Logic Deck and Incredible Surround™

- 2 x 120 watts RMS Stereo
- Max Sound for instant power boost
- Sound Navigation via Jog (6 Digital Sound Control & 6 Virtual Ambience Control)
- 3-step Dynamic Bass Boost
- Incredible Surround™
- Interactive Dashboard Display
- 3-way Bass Reflex Speaker System with Detachable Grilles
- Plays CD, CD-R and CD-RW discs
- FM/AM Digital Tuning with 40 presets
- Dual Logic Tape Deck with Auto Replay
- Bedroom Clock with Wake-up Alarm and Sleep-timer
- Eco Power Standby mode (<1 watt)
- 30-key Remote Control
- 4-Color Packaging



Let's make things better.



PHILIPS



Sound Enhancement

2 x 120 Watts RMS Stereo

120 watts continuous RMS power output per channel, at 6 Ohms, from 80Hz-16kHz, with no more than 10% Total Harmonic Distortion (THD).

Max Sound for instant power boost

A one-touch button sound setting for instant power boost which including extra bass performance and sound pressure level. It has designed to give extra boost with Digital Sound Control and Virtual Ambience Control sound settings.

Sound Navigation via jog (log + DSC + VAC)

The sound Navigation System is a complete set of sound manipulation tools consisting:

- 6 Digital Sound Control settings: (Digital, Pop, Classic, Rock, NewAge, Electric)
- 6 Virtual Ambience Control: (Hall, Cinema, Arcade, Concert, Disco, Cyber)

3-step Dynamic Bass Boost (DBB 1,2,3)

Bass reproduction is essential for deep and rich music, 3-step DBB offers the optimal level for any kind of music.

Incredible Surround™

An exciting, new, psycho-acoustic method of widening the stereo spatial image especially suited for applications with limited separation of left and right speakers.

3-Way Bass Reflex Speaker System

Equipped with one 5 1/4" woofer and one 2" ferro-fluid cooled tweeter and 1" Piezo. 3-way enclosures feature a wider range of frequency response for greater listening pleasure.

AM/FM Stereo Digital Tuner

State-of-the-art precision tuning system insures precise, accurate station selection every time, along with the greatest performance and reliability available.

Design

Design Concept

The attractive and shelf appealing emphasis on the sound control panel dominates and determines this range's character.

Detachable Cloth Speaker Grilles

Detachable cloth covered grilles protect delicate speaker components with rich, high-tech styling.

Convenience

3-CD Changer with Motorized Drawer

Multi-disc play capability provides more than three hours of continuous music.

Plays CD, CD-R and CD-RW discs

The player offers 100% playback guarantee of CD, CD-Recordable and CD Rewritable CD's over the entire lifetime of the player. Even CD-RW audio recordings on computers can be used.

Interactive Dashboard Display

An integrated Fluorescent Tube Display (FTD) Volume Unit (VU) Meter shows volume level and musical amplitude during playback.

Dual Logic Tape Deck

Offer the ability to switch from one function, such as fast forward, to another function, such as play by remote control.

Auto Replay

The feature employs an auto rewind mechanism to sense the end of the tape of the same side and automatically rewind and playback at the beginning of the tape providing an uninterrupted, continuous flow of music.

30-key Remote Control

This infrared remote control operates volume +/-, all CD functions (POWER, NEXT, PREVIOUS, PLAY, STOP, PAUSE, SHUFFLE, REPEAT, PROGRAM, CD123, CD DIRECT 1, 2, 3, ◀ and ▶), AUX/CDR select, TUNER select, TAPE 1/2 select, Timer ON/OFF, CLOCK, DISPLAY, SLEEP and sound enhancement features including MUTE, Digital Sound Control (DSC), Virtual Ambience Control (VAC), Incredible Surround™ (IS), Max on/off and Dynamic Bass Boost (DBB).

Plug & Play

Press play button for 5 secs to automatically program 40 tuner presets (FM only).

40-Random Channel Presets

Random memory presets allow pre-programming of up to 40 AM and FM station frequencies into the tuner memory.

Auto Store

Automatically stores up to 40 preset FM or AM stations.

40-Track CD Random Program

Store up to 40 of your favorite CD track selections, from one or multiple discs, to be played back in the order in which they are programmed anytime you like.

Auto Record Level Control

Micro electronic circuitry constantly monitors the final audio amplifier stage to insure accurate, distortion-free recordings everytime.

AUX/Video Input

For connection of audio accessory pieces such as a LD or DVD player, television, or external cassette deck.

Direct Source Selection

Automatically switch to a new source and pause the current source at the touch of a single button.

Demo Mode

Functions always. Press "STOP" for 5 secs to interrupt demo mode.

Direct Play Button

Allows you to select and play any CD in the carousel by touching only one button.

Change While Play

Flexibility of changing 2 discs while still listening to the third disc being played.

Repeat track/disc/all

Repeat your favorite track, disc or all.

Shuffle One/All Discs

Plays all selections on a particular disc or multiple discs in multi-disc players in random order, ignoring the sequential order in which they were originally recorded.

One-Touch CD Synchro Recording

One button allows the cassette deck and CD player to communicate with one another to synchronize the start of a recording on an analog audio cassette deck with the start of a CD or a CD program.

Next/Previous Skip

This two button feature offers you the opportunity to skip back to the previous track or skip up to the next track instantly.

Cassette Tape Dubbing

Cassette tape dubbing makes it possible to create good quality recordings (dubs) from one tape to another at normal speed in RECORD mode.

Clock, Alarm & Sleptimer

Set the alarm portion of a built-in digital clock to wake you to music from your favorite CD or an AM/FM radio station at any desired time of the day. Sleep timer settings of 60, 45, 30 or 15 minutes.

3 Display modes (including nite mode)

2 different display options showing different amounts of display activity can be selected and 1 nite mode display which shows minimal display activity and turns most of the lights off.

Eco Power Standby Mode (<1 watts)

Most systems consume 10-15 watts on standby. Philips system consume less than 1 watts energy on standby for big savings to the listener.

Stereo Headphone Jack

UPC Code: 0 3784990 7245

Product Dimensions:
10.6" W x 12.2" H x 15.4" D (electronics)
9.4" W x 12.2" H x 12.4" D (speakers)

Package Dimensions:
21.4" W x 28.3" H x 15.7" D
Product weight: 39.6 lbs.


Carton contains: 3CD Changer Mini System, Multi-Function Remote Control, Batteries, Operating instructions, Warranty information

Printed in Singapore
Date printed : Sep 2000
©2000 Royal Philips Electronics N.V.
All rights reserved.

A Division of Philips Electronics North America Corp.
Specifications subject to change without notice.

Incredible Surround™ is a Trademark of Philips Consumer Electronics Company

As an ENERGY STAR® Partner, Philips has determined that this product meets the ENERGY STAR® guidelines for energy efficiency.



Let's make things better.



PHILIPS