

Philips
Mini Hi-Fi System

MP3

FWM570



MP3 Playback with MAX Sound

For those who value technology that enhances experiences, FWM570 has it all. Immerse yourself in the power of Max Sound and fully appreciate your favorite MP3 music in dynamic and rich sound.

Powerful sound you can hear and feel

- Class 'D' Digital Amplifier for quality sound performance
- 3-way Speaker System with MAX bass port
- 2 x 110W RMS/2 x 220W music power/3000W PMPO

Longer listening, greater enjoyment

- Playback 30 hours of MP3-CD music
- 3 CD Changer
- Dual Logic Tape Deck with auto replay

Ready for gaming

- Gameport connection to your game console
- Game Sound modes for different types of games
- MIX-IT for mixing the game sound with your favorite music

PHILIPS
sense and simplicity

Specifications

Sound

- **Output Power:** 3000W PMPO
- **Sound Enhancement:** Class "D" Digital Amplifier, MAX Sound, Digital Sound Control, Dynamic Bass Boost, Virtual Ambience Control, Game Sound, MIX-IT

Loudspeakers

- **Main Speaker:** 3 way, Bass Reflex Speaker System, 6.5" woofer, 2" tweeter, Piezo, Speaker grilles detachable

Audio Playback

- **Playback Media:** CD, CD-R, CD-RW, MP3-CD
- **Loader Type:** 3 CD Carousel
- **Number of Discs:** 3
- **Disc Playback Modes:** Change 2 discs while playing, I, Fast Forward/Backward, Next/Previous Track Search, Repeat/one/all/program, Repeat/one/disk/program, 99-Track Programmable
- **Cassette Deck Technology:** Logic
- **Number of decks:** 2
- **Cassette Playback Modes:** Full Auto Stop, Autoreverse, Electronic Speed Control

Audio Recording

- **Recording Media:** Tape
- **Tape Recording Enhancement:** CD Synchro Start Recording, Automatic Recording Level

Tuner/Reception/Transmission

- Auto digital tuning
- **Tuner Bands:** FM Stereo, MW
- **Tuner Enhancements:** Auto Store, Easy Set (Plug & Play)
- **Station presets:** 40

Connectivity

- **Aux in:** Line in, Gameport
- **Headphone:** 3.5 mm
- **Other connections:** Composite video (CVBS) out, FM Antenna, MW Antenna

Convenience

- **Alarms:** CD Alarm, Radio Alarm, Sleep timer, Wake to favourite track
- **Clock:** On main display
- **Display Type:** FTD
- **Eco Power Standby:** 1 watt
- **Indications:** DIM mode, album name, album number, artis name, Cd functions, date, file name, time, track

Accessories

- **Remote control:** 32-key with 2xAA Batteries
- **Included Accessories:** AC Power Cord, FM/MW Antenna

Dimensions

- **Set dimensions (W x H x D):** 265 x 322 x 384 mm
- **Main speaker dimensions (W x H x D):** 242 x 310 x 245 mm
- **Packaging dimensions (W x H x D):** 510 x 412 x 624 mm
- **Weight incl. Packaging:** 20.5 kg

Power

- **Power supply:** 110-240V, 50/60 Hz
- **Standby power consumption:** < 1 W

Product highlights

Class D Amplifier

Class 'D' Digital Amplifier takes an analog signal, converts it into a digital signal and then amplifies the signal digitally. The signal then enters a demodulation filter to give the final output. The amplified digital output delivers all the advantages of digital audio, including improved sound quality. In addition, Class 'D' Digital Amplifier has greater than 90% efficiency compared to traditional AB amplifiers. This high efficiency translates into a powerful amplifier with a small footprint.

3-way spk sys with MAX port

2x110W RMS/2x220W music power

30 hours of MP3-CD music

3 CD Changer

Dual Logic Tape Deck

Gameport connection

Game Sound modes

MIX-IT for mixing game sound

