

Philips
Mini Hi-Fi System

MP3

FWM779



Remote Control MP3 Music from Your PC

Want to remote control the MP3 music from your PC that's turned into a massive MP3 Jukebox? With USB PC Link, you can! Plus Gameport and wOOx Technology that will greatly enhance your game and music pleasures via the FWM779's dynamic amplif

MP3 music at your fingertips

- Song title and playlist name display for easy navigation
- USB PC link turns your PC into a massive MP3 music jukebox

Ready for gaming

- Gameport connection to your game console
- Game Sound modes for different types of games
- MIX-IT for mixing the game sound with your favorite music

Longer listening, greater enjoyment

- Play 50 hours of MP3 music from CD

Powerful sound you can hear and feel

- Class 'D' digital amplifier for quality sound performance
- 2 x 250W RMS/2 x 500W music power/7500W PMPO
- Front firing wOOx Technology speakers

PHILIPS

Specifications

Sound

- Output Power: 2 x 500W music power
- Sound Enhancement: Class "D" Digital Amplifier, wOOx technology, Incredible Surround, Digital Sound Control, Virtual Ambience Control, Game Sound, MIX-IT

Loudspeakers

- Main Speaker: 3 way, Bass Reflex Speaker System, 6.5" woofer, wOOx Bass Radiator, 2" tweeter, Piezo, Speaker grilles detachable

Audio Playback

- Playback Media: CD, CD-R, CD-RW, MP3-CD
- Loader Type: Disc Tray Changer
- Number of Discs: 5
- Disc Playback Modes: Fast Forward/Backward, Next/Previous Track Search, Repeat/one/all/program, Repeat/one/disk/program, 99-Track Programmable, Change 2 discs while playing 1
- PC Link playback mode: By-pack Musicmatch software, USB connection

Tuner/Reception/Transmission

- Auto digital tuning
- Tuner Bands: FM Stereo, MW, LW
- Tuner Enhancements: Auto Store, Easy Set (Plug & Play)
- Station presets: 40
- RDS: Program Type, Radio Text, News, RDS Clock Set, Station Name

Connectivity

- Aux in: Line in, Gameport
- Headphone: 3.5 mm
- Other connections: Composite video (CVBS) out,

- FM Antenna, MW Antenna
- PC Link: USB 2.0

Convenience

- Alarms: CD Alarm, Radio Alarm, Sleep timer, Wake to favourite track
- Clock: On main display
- Display Type: FTD
- Eco Power Standby: 1 watt
- Indications: DIM mode, track, album name, album number, artis name, file name, time, date, Cd functions

Accessories

- Remote control: 32-key with 2xAA Batteries
- Included accessories: AC Power Cord, FM/MW Antenna

Dimensions

- Set dimensions (W x H x D): 265 x 322 x 390 mm
- Main speaker dimensions (W x H x D): 348 x 322 x 242 mm
- Packaging dimensions (W x H x D): 533 x 726 x 399 mm
- Weight incl. Packaging: 21.7 kg

Power

- Power supply: 110-240V, 50/60 Hz
- Standby power consumption: < 1 W

Software

- Philips Sound Agent 2
- USB PC Link driver

System Requirements

- CD-ROM drive
- USB: Free USB port

Highlights

Song title display

Song title and playlist name display for easy navigation

USB PC Link

USB PC Link lets you playback your MP3 music through the powerful speakers of Philips sound systems instead of your PC speakers. By connecting a PC directly to your audio system with a USB cable, you can stream MP3 music directly to your sound system, transforming your PC into a 'massive MP3 music jukebox'. The control buttons on the sound system and remote control provide easy navigation and control of the MP3 music stored in the MusicMatch Playlist. You can also view song title information as well as elapsed play time on the sound system's display.

Gameport connection

Gameport connection to your game console

Game Sound modes

Game Sound modes for different types of games

MIX-IT for mixing game sound

MIX-IT for mixing the game sound with your favorite music

50 hours of MP3-CD music

Play 50 hours of MP3 music from CD

Class 'D' Amplifier

Class 'D' Digital Amplifier takes an analog signal, converts it into a digital signal and then amplifies the signal digitally. The signal then enters a demodulation filter to give the final output. The amplified digital output delivers all the advantages of digital audio, including improved sound quality. In addition, Class 'D' Digital Amplifier has greater than 90% efficiency compared to traditional AB amplifiers. This high efficiency translates into a powerful amplifier with a small footprint.

2x250W RMS/2x500W music power
2 x 250W RMS/2 x 500W music power/7500W PMPO

Front firing wOOx Technology

Front firing wOOx Technology speakers



Issue date 2014-02-05

Version: 7.0.8

12 NC: 9073 100 11679
EAN: 87 10895 79147 2

© 2014 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com