


Mini DPL Hi-Fi System

FW-P78

**3 CD Changer with Dolby® Pro Logic Processor,  
Five Loudspeakers, 270 Watts Total Power &  
Powered subwoofer**

- 2 x 75 Watts + 40 Watts + 2 x 20 Watts RMS Stereo
- 40 Watts Powered Subwoofer
- 6-Speaker Dolby® Pro Logic Surround Sound System
- Sound Navigation and 26 Digital Sound Control modes
- 3-Step Dynamic Bass Boost
- 7-Band Spectrum Analyzer with 3 Display modes
- 3-Way Bass Reflex Speaker System with Detachable Grilles
- Magnetically Shielded (Front and Center Speakers)
- CD-Rewritable Compatible
- 40-Track CD Random Program
- AM/FM Stereo Digital Tuning with 40 Presets
- Dual Logic Tape Deck with Auto Reverse
- Digital Recording Ready (digital and line out)
- Subwoofer ready
- Easy set for radio
- Energy Saving Standby mode (<2 watts)
- Bedroom Clock with Wake-up Alarm + Sleep Timer
- Easy Hook up via Color Coded Cables
- 33-Button Remote Control
- 4-Color Packaging



Let's make things better.



PHILIPS

### Sound Enhancement

#### 2 x 75 Watts + 40 Watts + 2 x 20 Watts Dolby® Pro Logic Output Mode, 40 Watts Powered Subwoofer

75 Watts L/R front, 40 Watts center, 20 Watts L/R rear and 40 Watts subwoofer RMS power output power per channel, at 6 Ohms, from 80Hz-16kHz, with no more than 10% Total Harmonic distortion (THD).

#### 6-Speaker Dolby® Pro Logic Surround Sound System

Provides the current industry standard for home theater sound from VCR and laserdisc movies. The front left and right speakers deliver detailed, directional sound as the center channel speaker "steers" dialogue/vocal sound to where you see the mouth moving - at the TV screen. Both surround speakers add a greater sense of depth with special effects and time delay making every living room a home theater with spaceships overhead, aliens behind the couch but no gum on the floor. The subwoofer enhances this home theater effect.

#### Magnetic Shielding

Left front, right front, and center speakers are all equipped with magnetic shielding to prevent interference with color television picture tube purity.

#### 3-Way Bass Reflex Speaker System

Equipped with one 6 1/2" woofer for smooth low and mid range reproduction, one 2 1/2" ferro-fluid cooled tweeter and one 1" Polydome tweeter for crisp high tones.

#### Sound Navigation

The JOG SHUTTLE of this feature adds a new dimension in fine-tuning the sound settings to suit your personal taste.

#### 26-step Digital Sound Control

The feature offers 26 different sound settings based on 6 basic settings: (CLASSIC - 1 setting, ROCK - 5 settings, VOCAL - 5 settings, TECHNO - 5 settings, OPTIMAL - 5 settings, JAZZ - 5 settings)

#### 3-Step Dynamic Bass Boost (Beat, Punch, Blast)

Bass reproduction is essential for deep and rich music. 3 Step DBB offers the optimal level for any kind of music.

#### AM/FM Stereo Digital Tuner

State-of-the-art precision tuning system insures precise, accurate station selection every time, along with the greatest performance and reliability available.

### Convenience

#### 3-CD Changer with Motorized Drawer

Multi-disc play capability provides more than three hours of continuous music.

#### CD-Rewritable Compatible

The player offers 100% playback guarantee of Cd-Rewritable CD@s over the entire lifetime of the player. Even CD-RW audio recordings on computers can be used.

#### Dual Logic Tape Deck

Offer the ability to switch from one function, such as fast forward, to another function, such as play, by remote control.

#### Auto Reverse

The feature employs an auto reverse mechanism to sense the end of the tape and automatically reverse the direction of tape travel in the PLAY mode providing an uninterrupted, continuous flow of music without manually flipping the cassette tape.

### 33-Button Remote Control

This infrared remote control operates volume +/-, all CD functions (POWER, NEXT, PREVIOUS, PLAY, STOP, PAUSE, SHUFFLE, REPEAT, PROGRAM, CD DIRECT 1, 2, 3, SIDE, ►► and ◀◀), AUX select, TUNER select, TAPE 1/2 select, TV select, SLEEP TIMER select and sound enhancement features including MUTE, Surround, Dynamic Bass Boost, Digital Sound Control and the Dolby® Prologic mode select, Test Tone select, Balance L/R, Center +/- and Rear +/-.

#### Easy Set

Press Standby 'ON' for 5 secs to automatically program 40 tuner presets.

#### 40-Random Channel Presets

Random memory presets allow pre-programming of up to 40 AM and FM station frequencies into the tuner memory.

#### Auto Store

Automatically stores up to 40 preset FM or AM stations.

#### 40-Track CD Random Program

Store up to 40 of your favorite CD track selections, from one or multiple discs, to be played back in the order in which they are programmed anytime you like.

#### AUX/Video Input

For connection of audio accessory pieces such as a LD or DVD player, television, or external cassette deck.

#### Demo Mode

Functions always. Press "STOP" for 5 secs to interrupt demo mode.

#### Direct Play Button

Allows you to select and play any CD in the carousel by touching only one button.

#### Change While Play

Flexibility of changing 2 discs while still listening to the third disc being played.

#### One-Touch CD Synchro Recording

One button allows the cassette deck and CD player to communicate with one another to synchronize the start of a recording on an analog audio cassette deck with the start of a CD or a CD program.

#### Repeat track

Repeat your favorite track.

#### Shuffle One/All Discs

Plays all selections on a particular disc or multiple discs in multi-disc players in random order, ignoring the sequential order in which they were originally recorded.

#### Next/Previous Skip

This two button feature offers you the opportunity to skip back to the previous track or skip up to the next track instantly.

#### High-Speed Dubbing

High-speed dubbing makes it possible to create good quality recordings (dubs) from one tape to another at twice the normal speed in RECORD mode.

#### Easy Hook up with Color Coded Cables

Center - Blue/Black

Front - Red/Black

Rear - Grey/White

#### 3 Dim Display modes (including nite mode)

2 different display options showing different amounts of display activity can be selected and 1 nite mode display which shows minimal display activity and turns most of the lights off.

### Clock/Timer and Sleptimer

Set the alarm portion of a built-in digital clock to wake you to music from your favorite CD or an AM/FM radio station at any desired time of the day. Sleptimer settings of 60, 45, 30 or 15 minutes.

### Stereo Headphone Jack

### Design

#### Design Concept

The attractive and shelf appealing emphasis on the sound control panel dominates and determines this range's character. The sound control panel emphasis which supports the entire sound story is reinforced by 2 distinctive rotaries (sound jog and volume) that builds itself logically up the range with features, finishing, colours and product design detail differentiation.


Uninterrupted display and cassette window lens set on a strong underlying profile gives strong rational while the use of appropriate backlighting, lightstrips and rings coupled with choice colours evokes the emotional appeal.

#### Oversized, MultiColor, Digital FTD Display

This large display is easy to read at any distance with no distortion or distraction and the multi-color format makes it easy to recognize different functions at a glance.

#### Detachable Cloth Speaker Grilles

Detachable cloth covered grilles protect delicate speaker components with rich, high-tech styling.



UPC Code: 0 37849 89359 3

Product Dimensions:

10.4" W x 12.2" H x 15.4" D (electronics)

9.4" W x 12.2" H x 12.4" D (speakers)

10.4" W x 5.5" H x 9.4" D (center speakers)

9.2" W x 4.1" H x 8.8" D (surround speakers)

7.9" W x 12.2" H x 14.6" D (subwoofer)

Package Dimensions:

39.3" W x 28.2" H x 14.3" D

Product weight: 61.7 lbs.

Carton contains: 3CD Changer Mini System, Subwoofer, Multi-Function

Remote Control, Batteries, Operating instructions, Warranty information

Printed in Singapore

Date printed: Oct 1999

©1999 Royal Philips Electronics N.V.

A Division of Philips Electronics North America Corp.

Specifications subject to change without notice.

Dolby® and Dolby® Pro Logic are trademarks of Dolby Laboratories

As an ENERGY STAR® Partner, Philips has determined that this product meets the ENERGY STAR® guidelines for energy efficiency

Let's make things better.



PHILIPS