

PHILIPS

Steam iron

FeatherLight

Steam 13g/min

Non-stick soleplate

Anti-calc

1200 Watts



GC1418/36



Removes creases faster*

Reduces your ironing time up to 30%

There's so much more to life than household chores, so you want to get them done as quickly as possible. With its continuous steam, shot of steam and spray functions this iron is designed to easily remove even the most stubborn creases.

Comfortable ironing

- 360° swivel for easy maneuverability
- Variable steam settings to suit every garment
- Watertank filling door prevents water spilling

Longer lifetime


- Calc clean slider to easily remove scale out of your iron

Easily removes creases

- A fine spray evenly moistens the fabric
- Continuous steam output up to 13 g/min
- Non-stick soleplate coating
- Steam boost up to 60g for the most stubborn creases

Highlights

Spray



The spray function produces a fine mist that evenly moistens the fabric, making it easier to iron out creases.

Calc clean slider




This steam iron can be operated with normal tap water and the calc clean slider makes it easy to remove any built-up scale out of your iron. To maintain the performance of your Philips steam iron, you should use this scale clean function once a month when using normal tap water.

Continuous steam output



Continuous steam output up to 13 g/min

Non-stick soleplate



The soleplate of your Philips iron is coated with a special non-stick layer for good gliding performance on all fabrics.


360° swivel

With this flexible swivel, which rotates in all directions, it is easier to maneuver the iron over the board

Variable steam settings

Variable steam settings let you select the perfect amount of steam for each fabric, so you get professional ironing results.

Watertank filling door



Water tank filling door to prevent the water from spilling accidentally from the watertank

Steam boost up to 60 g



The iron's 60 g steam boost enables you to easily remove even the most stubborn creases.

Specifications

Fast & powerful crease removal

Soleplate: Non-stick
 Continuous steam output: 13 g/min
 Steam boost: 60 g
 Variable steam settings
 Spray
 Power: 1200 W

Easy to use

Power cord length: 1.8 m
 Cord freedom (swivel): 360 degree cord freedom

Calc management

Calc clean solution: Self clean

