

# PHILIPS

Lightweight steam iron  
with non-stick soleplate

Featherlight Plus

Steam 15 g/min

60 g steam boost

Non-stick soleplate

Calc-clean



GC1424/40



## Iron 30% faster with steam\*

With continuous steam, non-stick coating and a built-in water spray, this lightweight steam iron is designed to remove wrinkles from garments quickly.

### Longer lifetime

- Calc-clean to extend iron's life by years

### Easy to use

- Comfortable handle and stable heel rest for extra stability
- Integrated water spray to make ironing easier
- Large filling door to prevent water spilling
- Large temperature control dial for different kinds of fabrics
- Triple precision tip for optimal control and visibility

### Fast crease removal

- Non-stick soleplate coating
- Power up to 1400 W enabling constant high steam output
- Continuous steam up to 15 g/min for fast crease removal
- Steam boost up to 60 g

# Highlights

## Non-stick soleplate



The soleplate of your Philips iron is coated with a special non-stick layer for good gliding performance on all fabrics.

## Integrated water spray



The spray function produces a fine mist that evenly moistens the fabric, making it easier to iron out creases.

## Triple precision tip



The tip of this Philips iron is precise in 3 ways: it has a pointed tip, button groove and a sleek nose design. The triple precision tip enables you to reach even the most tricky areas, e.g. around the buttons or between the pleats.

## Power up to 1400 W



Power up to 1400 W enabling constant high steam output.

## Large filling door



Large filling door to prevent water spilling accidentally.

## Continuous steam up to 15 g/min



Continuous steam up to 15 g/min for fast crease removal.

## Calc-clean



Calc-clean to extend iron's life by years

## Temperature control dial



The large temperature control dial allows you to adjust easily to the right ironing temperature for each kind of fabric, so you can achieve your desired results safely.

## Steam boost up to 60 g



Steam output is measured in grams of weight as it leaves the soleplate. The heavier the output, the deeper the steam can reach into the fabric layers for longer-lasting crease removal. This steam iron has a 60 g steam boost for stubborn crease removal.

## Comfortable handle and stable



Comfortable handle and stable heel rest for extra stability

# Specifications

## Fast crease removal

Continuous steam: 15 g/min  
Power: 1400 W  
Steam boost: 60 g  
Water spray

## Easy to use

Soleplate name: Non-stick  
Water tank capacity: 160 ml  
Precision steam tip

## Scale management

Descaling and cleaning: Self-clean

## Size and weight

Packaging dimensions (W x H x D): 27 x 1.5 x 11.4 cm  
Total weight with packaging: 0.95 kg  
Weight of iron: 0.78 kg

