

# PHILIPS

Steam iron with  
non-stick soleplate

Featherlight Plus

Steam 18 g/min

65 g steam boost

Non-stick soleplate

Calc-clean



GC1426/30



## Iron 30% faster with steam\*

There's so much more to life than household chores, so you want to get them done as fast as possible. With continuous steam, non-stick coating and a built-in water spray, this iron is designed to remove wrinkles from garments quickly.

### Fast crease removal

- Continuous steam up to 18 g/min for fast crease removal
- Steam boost up to 65 g
- Power up to 1400 W enabling constant high steam output
- Non-stick soleplate coating

### Easy to use

- Large temperature control dial for different kind of fabrics
- Integrated water spray for making ironing easier
- Triple precision tip for optimal control and visibility
- Comfortable handle and stable heel rest for extra stability
- Large filling door for preventing water spilling

### Longer lifetime

- Calc-clean for extending iron's life for years

# Highlights

## Calc-clean



Calc-clean for extending iron's life for years

## Comfortable handle and stable



Comfortable handle and stable heel rest for extra stability

## Continuous steam up to 18 g/m



Continuous steam up to 18 g/min for fast crease removal.

## Integrated water spray




The spray function produces a fine mist that evenly moistens the fabric, making it easier to iron out creases.

## Large filling door



Large filling door to prevent accidental water spilling.

## Temperature control dial



The large temperature control dial lets you easily adjust to the right ironing temperature for each kind of fabric, so you can achieve your desired results safely.

## Non-stick soleplate



The soleplate of your Philips iron is coated with a special non-stick layer for good gliding performance on all fabrics.

## Power up to 1400 W



Power up to 1400 W enabling constant high steam output.

## Steam boost up to 65 g



Steam output is measured in grams of weight as it leaves the soleplate. The heavier the output the deeper the steam can reach into the fabric layers for longer lasting crease removal. This steam iron has a 65 g steam boost for stubborn crease removal.

## Triple precision tip



The tip of this Philips iron is precise in 3 ways: it has a pointed tip, button groove and a sleek design of the nose. Triple Precision tip enables you to reach even into the most tricky areas, e.g. around the buttons or between the pleats.

# Specifications

## Fast crease removal

Continuous steam: 18 g/min  
Power: 1400 W  
Steam boost: 65 g  
Water spray

## Easy to use

Soleplate name: Non-stick  
Water tank capacity: 160 ml  
Precision steam tip

## Scale management

Descaling and cleaning: Self clean

## Size and weight

Packaging dimensions (WxHxL):  
27x14.5x11.4 cm  
Total weight with packaging: 0.95 kg  
Weight of iron: 0.78 kg

