


# PHILIPS

## Steam iron

2000 W

Anti-calc

Non-stick soleplate



GC1432



## Easy and Effective

### 3 ways to make your ironing easier

This comfort steam iron makes your ironing easy and effective with lots of continuous steam and the non-stick soleplate soleplate makes your gliding easier. With comfort iron the ironing job is now made simpler.

#### Easy gliding on all fabrics

- Easy gliding on all ironable garments

#### Longer lifetime

- Calc clean slider to easily remove scale out of your iron

#### Easy to remove creases

- A fine spray evenly moistens the fabric
- Continuous steam up to 25g/min for good crease removal
- Power up to 2000 W enabling constant high steam output

#### Easy to start ironing

- Large water tank 220ml and convenient water filling
- Bigger temperature dial for easier temperature adjustment
- Triple precision tip for optimal control and visibility

# Highlights

## Spray

The spray function produces a fine mist that evenly moistens the fabric, making it easier to iron out creases.

## Triple precision tip

The tip of this Philips iron is precise in 3 ways: it has a pointed tip, button groove and a sleek design of the nose. Triple Precision tip enables you to reach even into the most tricky areas, e.g. around the buttons or between the pleats.

## Power up to 2000 W

Power up to 2000 W enables constant high steam output.

## Non stick soleplate

The soleplate of your Philips iron is coated with a special non-stick layer for easy gliding performance on all ironable garments.

## Large water tank

Less refilling with the extra-large 220 ml water tank so you can iron more clothes in one go.

## Temperature dial

Bigger temperature dial for easier temperature adjustment

## Continuous steam up to 25g/min



Continuous steam up to 25g/min for good crease removal.

## Calc clean slider

This steam iron can be operated with normal tap water and the calc clean slider makes it easy to remove any built-up scale out of your iron. To maintain the performance of your Philips steam iron, you should use this scale clean function once a month when using normal tap water.

# Specifications

## Fast crease removal

Voltage: 240 V

Water spray

## Easy to use

Soleplate name: Non-stick

Water tank capacity: 220 ml

Precision steam tip

Refill any time during use

## Fast & powerful crease removal

Continuous steam output: 25 g/min

Power: 2000 W

## Scale management

Descaling and cleaning: Self clean

## Green efficiency

User manual: 100% recycled paper

