

PHILIPS

Steam iron

2000 W

Anti-calc

Non-stick soleplate



GC1433/40



Easy and Effective

Three ways to make your ironing easier

This comfort steam iron makes your ironing easy and effective by providing plenty of continuous steam, and the non-stick soleplate makes gliding smoother. With the comfort iron, ironing is made simple.

Easy to remove creases

- Power up to 2000 W, enabling constant high-steam output
- Continuous steam up to 25 g/m for efficient crease removal
- Steam boost up to 90 g for the most stubborn creases
- A fine spray evenly moistens the fabric

Easy gliding on all fabrics

- Easy gliding on all iron-suitable garments

Easy to start ironing

- Large 220 ml water tank that makes water filling convenient
- Larger temperature dial for easier temperature adjustment
- Triple precision tip for optimal control and visibility

Longer lifetime

- Calc clean slider to easily remove scale out of your iron

Highlights

Power up to 2000 W



Power up to 2000 W enables constant high-steam output.

Continuous steam up to 25 g/m



Continuous steam up to 25 g/m for efficient crease removal.

Steam boost up to 90 g



The iron's 90 g steam boost enables you to easily remove even the most stubborn creases.

Spray



The spray function produces a fine mist that evenly moistens the fabric, making it easier to iron out creases.

Non-stick soleplate



The soleplate of your Philips iron is coated with a special non-stick layer for easy gliding performance on all iron-suitable garments.

Large water tank



Less frequent refilling with the extra-large, 220 ml water tank, so you can iron more clothes in one go.

Temperature dial



Larger temperature dial for easier temperature adjustment

Triple precision tip



The tip of this Philips iron is precise in 3 ways: it has a pointed tip, button groove and a sleek nose design. The triple precision tip enables you to reach even the most tricky areas, e.g. around the buttons or between the pleats.

Calc clean slider



This steam iron can be operated with normal tap water, and the calc clean slider makes it easy to remove any built-up scale from your iron. To maintain the performance of your Philips steam iron, you should use this scale clean function once a month when using normal tap water.

Specifications

Calc management

Calc clean solution: Self-clean

Easy to use

Ultra-light and comfortable

Water tank capacity: 220 ml

Filling and emptying water: Large filling hole

Fast and powerful crease removal

Continuous steam output: 25 g/min

Power: 2000 W

Soleplate: Non-stick

Spray

Steam boost: 90 g

Steam tip

Sustainability

User manual: 100% recycled paper

Technical specifications

Voltage: 240 V

