



Steam iron

- 2000 W
- Anti-calc
- Non-stick soleplate

GC1434/20

Easy and Effective

Three ways to make your ironing easier

This comfort steam iron makes your ironing easy and effective by providing plenty of continuous steam, and the non-stick soleplate makes gliding smoother. With the comfort iron, ironing is made simple.

Benefits

Easy gliding on all fabrics

- Easy gliding on all iron-suitable garments

Longer lifetime

- Calc clean slider to easily remove scale out of your iron

Easy to remove creases

- Power up to 2000 W, enabling constant high-steam output
- Continuous steam up to 25 g/min for good crease removal

- Steam boost up to 90 g for the most stubborn creases
- A fine spray evenly moistens the fabric

Easy to start ironing

- Large 220 ml water tank that makes water filling convenient
- Larger temperature dial for easier temperature adjustment
- Triple precision tip for optimal control and visibility

PHILIPS

Features

Power up to 2000 W



Power up to 2000 W enables constant high steam output.

Continuous steam up to 25 g/min



Continuous steam up to 25 g/min for good crease removal.

Steam boost up to 90 g



The iron's 90 g steam boost enables you to easily remove even the most stubborn creases.

Spray



The spray function produces a fine mist that evenly moistens the fabric, making it easier to iron out creases.

Non-stick soleplate




The soleplate of your Philips iron is coated with a special non-stick layer for easy gliding performance on all iron-suitable garments.

Large water tank



Less frequent refilling with the extra-large, 220 ml water tank, so you can iron more clothes in one go.

Temperature dial



Triple precision tip



The tip of this Philips iron is precise in 3 ways: it has a pointed tip, button groove and a sleek nose design. The triple precision tip enables you to reach even the most tricky areas, e.g. around the buttons or between the pleats.

Calc clean slider



This steam iron can be operated with normal tap water, and the calc clean slider makes it easy to remove any built-up scale from your iron. To maintain the performance of your Philips steam iron, you should use this scale clean function once a month when using normal tap water.

Specifications

Please note that this is a pre-sales leaflet. The contents of this leaflet reflect the best of our knowledge per date and country mentioned above. The contents of this leaflet are subject to change without notice. Philips does not accept any liability as to the contents of this leaflet.

Fast crease removal

Continuous steam	25 g/min
Power	2000 W
Steam boost	90 g

Easy to use

Water tank capacity	220 ml
---------------------	--------

Packaging dimensions

Height	14.60 cm
Width	29.00 cm
Depth	12.70 cm
Net weight	0.90 kg
Gross weight	1.17 kg
EAN	08710103870135
Number of products included	1
Country of origin	CN
Harmonised Systems Code	851640

Outer Carton

Length	39.00 cm
Width	30.00 cm
Height	31.20 cm
Gross weight	7.40 kg
EAN	18710103870132
Number of consumer packages	6



data subject to change
2018, November 15

Version: 2.1.1
EAN: 08710103870135

© 2018 Koninklijke Philips N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. or their respective owners.

www.philips.com