

PHILIPS

Steam iron

2000 W

Anti-calc

Non-stick soleplate

GC1434/70



Easy and Effective

3 ways to make your ironing easier

This comfort steam iron makes your ironing easy and effective with lots of continuous steam and the non-stick soleplate soleplate makes your gliding easier. With comfort iron the ironing job is now made simpler.

Easy gliding on all fabrics

- Easy gliding on all ironable garments

Longer lifetime

- Calc clean slider to easily remove scale out of your iron

Easy to remove creases

- A fine spray evenly moistens the fabric
- Continuous steam up to 25g/min for good crease removal
- Power up to 2000 W enabling constant high steam output
- Steam boost up to 90 g for the most stubborn creases

Easy to start ironing

- Large water tank 220ml and convenient water filling
- Bigger temperature dial for easier temperature adjustment
- Triple precision tip for optimal control and visibility

Highlights

Power up to 2000 W



Power up to 2000 W enables constant high steam output.

Continuous steam up to 25g/min



Continuous steam up to 25g/min for good crease removal.

Steam boost up to 90 g



The iron's 90 g steam boost enables you to easily remove even the most stubborn creases.

Spray



The spray function produces a fine mist that evenly moistens the fabric, making it easier to iron out creases.

Non stick soleplate




The soleplate of your Philips iron is coated with a special non-stick layer for easy gliding performance on all ironable garments.

Large water tank



Less refilling with the extra-large 220 ml water tank so you can iron more clothes in one go.

Temperature dial



Bigger temperature dial for easier temperature adjustment

Triple precision tip



The tip of this Philips iron is precise in 3 ways: it has a pointed tip, button groove and a sleek design of the nose. Triple Precision tip enables you to reach even into the most tricky areas, e.g. around the buttons or between the pleats.

Calc clean slider



This steam iron can be operated with normal tap water and the calc clean slider makes it easy to remove any built-up scale out of your iron. To maintain the performance of your Philips steam iron, you should use this scale clean function once a month when using normal tap water.

Specifications

Easy to use

Water tank capacity: 220 ml

Fast crease removal

Continuous steam: 25 g/min

Power: 2000 W

Steam boost: 90 g

