

PHILIPS

Philips steam iron

2000 W

Anti-calc

Non-stick soleplate

Drip-stop



GC1436/20



Easy and Effective

Three ways to make your ironing easier

This comfort steam iron makes your ironing easy and effective by providing plenty of continuous steam, and the non-stick soleplate makes gliding smoother. With the comfort iron, ironing is made simple.

Easy to remove creases

- Power up to 2000 W, enabling constant high-steam output
- Continuous steam up to 25 g/min for good crease removal
- A fine spray evenly moistens the fabric
- 100 g steam boost to remove stubborn creases easily

Easy gliding on all fabrics

- Easy gliding on all iron-suitable garments

Easy to start ironing

- Drip-stop system keeps your garments spotless while ironing
- Large 220 ml water tank that makes water filling convenient
- Larger temperature dial for easier temperature adjustment
- Triple precision tip for optimal control and visibility

Longer lifetime

- Calc clean slider to easily remove scale out of your iron

Highlights

Power up to 2000 W



Power up to 2000 W enables constant high steam output.

Steam boost up to 100 g



Steam boost up to 100 g for fast removal of even the most stubborn creases.

Continuous steam up to 25 g/min



Continuous steam up to 25 g/min for good crease removal.

Spray



The spray function produces a fine mist that evenly moistens the fabric, making it easier to iron out creases.

Non-stick soleplate



The soleplate of your Philips iron is coated with a special non-stick layer for easy gliding performance on all iron-suitable garments.

Large water tank



Less frequent refilling with the extra-large, 220 ml water tank, so you can iron more clothes in one go.

Temperature dial



Larger temperature dial for easier temperature adjustment

Drip-stop system



Drip-Stop system lets you iron delicate fabrics at low temperatures without having to worry about stains from water droplets.

Triple precision tip



The tip of this Philips iron is precise in 3 ways: it has a pointed tip, button groove and a sleek nose design. The triple precision tip enables you to reach even the most tricky areas, e.g. around the buttons or between the pleats.

Calc clean slider



This steam iron can be operated with normal tap water, and the calc clean slider makes it easy to remove any built-up scale from your iron. To maintain the performance of your Philips steam iron, you should use this scale clean function once a month when using normal tap water.

Specifications

Easy to use

Drip-stop

Water tank capacity: 220 ml

Soleplate name: Non-stick

Fast crease removal

Continuous steam: 25 g/min

Power: 2000 W

Steam boost: 100 g

