

# PHILIPS

## Steam iron

2000 W

Anti-calc

Non-stick soleplate

Drip stop



GC1436/20



## Easy and Effective

### 3 ways to make your ironing easier

This comfort steam iron makes your ironing easy and effective with lots of continuous steam and the non-stick soleplate soleplate makes your gliding easier. With comfort iron the ironing job is now made simpler.

#### Easy to remove creases

- Power up to 2000 W enabling constant high steam output
- Continuous steam up to 25g/min for good crease removal
- A fine spray evenly moistens the fabric
- 100 g steam boost to remove stubborn creases easily

#### Easy gliding on all fabrics

- Easy gliding on all ironable garments

#### Easy to start ironing

- Drip-stop system keeps your garments spotless while ironing
- Large water tank 220ml and convenient water filling
- Bigger temperature dial for easier temperature adjustment
- Triple precision tip for optimal control and visibility

#### Longer lifetime

- Calc clean slider to easily remove scale out of your iron

# Highlights

## Power up to 2000 W



Power up to 2000 W enables constant high steam output.

## Steam boost up to 100 g



Steam boost up to 100g for fast removal of even the most stubborn creases.

## Continuous steam up to 25g/min



Continuous steam up to 25g/min for good crease removal.

## Spray



The spray function produces a fine mist that evenly moistens the fabric, making it easier to iron out creases.

## Non stick soleplate




The soleplate of your Philips iron is coated with a special non-stick layer for easy gliding performance on all ironable garments.

## Large water tank



Less refilling with the extra-large 220 ml water tank so you can iron more clothes in one go.

## Temperature dial



Bigger temperature dial for easier temperature adjustment

## Drip stop system



Drip Stop system lets you iron delicate fabrics at low temperatures without having to worry about stains from water droplets.

## Triple precision tip



The tip of this Philips iron is precise in 3 ways: it has a pointed tip, button groove and a sleek design of the nose. Triple Precision tip enables you to reach even into the most tricky areas, e.g. around the buttons or between the pleats.

## Calc clean slider



This steam iron can be operated with normal tap water and the calc clean slider makes it easy to remove any built-up scale out of your iron. To maintain the performance of your Philips steam iron, you should use this scale clean function once a month when using normal tap water.

# Specifications

## Easy to use

Drip stop

Water tank capacity: 220 ml

Soleplate name: Non-stick

## Fast crease removal

Continuous steam: 25 g/min

Power: 2000 W

Steam boost: 100 g

