



#### Steam iron

- 2000 W
- Anti-calc
- Non-stick soleplate
- Drip stop

GC1436/20

## Easy and Effective

### Three ways to make your ironing easier

This comfort steam iron makes your ironing easy and effective by providing plenty of continuous steam, and the non-stick soleplate makes gliding smoother. With the comfort iron, ironing is made simple.

#### Benefits

##### Easy to remove creases

- Power up to 2000 W, enabling constant high-steam output
- 100 g steam boost to remove stubborn creases easily
- Continuous steam up to 25 g/m for efficient crease removal
- A fine spray evenly moistens the fabric

##### Easy gliding on all fabrics

- Easy gliding on all iron-suitable garments

##### Easy to start ironing

- Large 220 ml water tank that makes water filling convenient
- Larger temperature dial for easier temperature adjustment
- Drip-stop system keeps your garments spotless while ironing
- Triple precision tip for optimal control and visibility

##### Longer lifetime

- Calc clean slider to easily remove scale out of your iron

**PHILIPS**

## Features

### Power up to 2000 W



Power up to 2000 W enables constant high steam output.

### Steam boost up to 100 g



Steam boost up to 100 g for fast removal of even the most stubborn creases.

### Continuous steam up to 25 g/m



Continuous steam up to 25 g/m for efficient crease removal.

### Spray



The spray function produces a fine mist that evenly moistens the fabric, making it easier to iron out creases.

### Non-stick soleplate




The soleplate of your Philips iron is coated with a special non-stick layer for easy gliding performance on all iron-suitable garments.

### Large water tank



Less frequent refilling with the extra-large, 220 ml water tank, so you can iron more clothes in one go.

### Temperature dial



### Drip stop system



Drip-Stop system lets you iron delicate fabrics at low temperatures without having to worry about stains from water droplets.

### Triple precision tip



The tip of this Philips iron is precise in 3 ways: it has a pointed tip, button groove and a sleek nose design. The triple precision tip enables you to reach even the most tricky areas, e.g. around the buttons or between the pleats.

### Calc clean slider



This steam iron can be operated with normal tap water, and the calc clean slider makes it easy to remove any built-up scale from your iron. To maintain the performance of your Philips steam iron, you should use this scale clean function once a month when using normal tap water.

## Specifications

Please note that this is a pre-sales leaflet. The contents of this leaflet reflect the best of our knowledge per date and country mentioned above. The contents of this leaflet are subject to change without notice. Philips does not accept any liability as to the contents of this leaflet.

### Easy to use

Drip stop	Yes
Water tank capacity	220 ml
Soleplate name	Non-stick

### Fast crease removal

Continuous steam	25 g/min
------------------	----------

Power 2000 W  
Steam boost 100 g

Harmonised Systems Code 851640

#### Packaging dimensions

Height 14.60 cm  
Width 29.00 cm  
Depth 12.70 cm  
Net weight 0.90 kg  
Gross weight 1.17 kg  
EAN 08710103751427  
Number of products included 1  
Country of origin CN

#### Outer Carton

Length 30.00 cm  
Width 39.00 cm  
Height 31.20 cm  
Gross weight 7.46 kg  
EAN 18710103751424  
Number of consumer packages 6



data subject to change  
2018, January 13

Version: 4.2.1  
EAN: 08710103751427

© 2018 Koninklijke Philips N.V.  
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. or their respective owners.

[www.philips.com](http://www.philips.com)