

PHILIPS

Steam iron

2000 W

Anti-calc

Ceramic soleplate

Drip stop



GC1442/27



Easy and Effective

3 ways to make your ironing easier

This iron makes your ironing easy and effective with lots of continuous steam. The durable ceramic soleplate glides well over all garments, and the 3x precision tip reaches the trickiest areas. With the Comfort iron, ironing is made simple

Keeps your garments looking like new

- Fabric shaver for removing pills from all types of garment

Easy to remove creases

- A fine spray evenly moistens the fabric
- Continuous steam up to 25g/min for good crease removal
- Power up to 2000 W enabling constant high steam output
- Steam boost up to 100 g for the most stubborn creases

Easy gliding on all fabrics

- Durable ceramic soleplate for good gliding on all garments

Easy to start ironing

- Large water tank 220ml and convenient water filling
- Triple precision tip for optimal control and visibility
- Drip-stop system keeps your garments spotless while ironing

Highlights

Fabric Shaver

Easily removes fabric pills from all types of garments. All your garments, whether it is your sweater or your blanket, will look like new again.

Spray



The spray function produces a fine mist that evenly moistens the fabric, making it easier to iron out creases.

Continuous steam up to 25g/min



Continuous steam up to 25g/min for good crease removal.

Power up to 2000 W



Power up to 2000 W enables constant high steam output.

100 g steam boost



Applying the steam boost will release a steam shot up to 100 g to remove even the toughest creases.

Good gliding and durability



Our durable ceramic soleplate glides well on all garments. It's non-stick, scratch-resistant and simple to keep clean.

Large water tank



Less refilling with the extra-large 220 ml water tank so you can iron more clothes in one go.

Triple precision tip



The tip of this Philips iron is precise in 3 ways: it has a pointed tip, button groove and a sleek design of the nose. Triple Precision tip enables you to reach even into the most tricky areas, e.g. around the buttons or between the pleats.

Drip stop system



Drip Stop system lets you iron delicate fabrics at low temperatures without having to worry about stains from water droplets.

Specifications

Fast crease removal

Voltage: 240 V

Continuous steam: 25 g/min

Power: 2000 W

Steam boost: 100 g

Easy to use

Water tank capacity: 220 ml

Precision steam tip

Drip stop

Scale management

Descaling and cleaning: Built-in Calc Clean Slider

Green efficiency

User manual: 100% recycled paper

