

# PHILIPS

## Dry iron

GC148



## Simple, fast and effective

### Lightweight, quality iron

This high quality lightweight iron is designed to iron your clothes in a simple and effective way.

#### **Easy gliding on all fabrics**

- Ceralon soleplate for better gliding on all fabrics

#### **Reaches into tricky areas**

- Button groove speeds up ironing along buttons and seams

#### **Full control**

- Iron temperature-ready light

#### **Easy setup and storage**

- Cord winder to conveniently store the main cord

# Highlights

## Ceralon soleplate

Ceralon soleplate for better gliding on all fabrics.

## Cord winder

The cord can be wrapped around the heelrest, so that the appliance is easy to store.

# Specifications

## Fast & powerful crease removal

Power: 950 - 1100 W

Soleplate: Non-stick

## Easy to use

Power cord length: 1.8 m

## Technical specifications

Product dimensions: 25.5 x 11.1 x 12.8 cm

Voltage: 220 - 240

Weight of iron: 0.76 kg

