

PHILIPS

Dry iron

DynaGlide soleplate

6 ft. (1.8 m) cord length

1200 Iron Watts

1200 Watts



GC160/02



The best gliding soleplate

For Philips dry irons

Discover the new Philips dry iron with DynaGlide soleplate. The slim tip soleplate, comfortable textured handle and elevated temperature control make the iron easy to use.

Easy gliding on all fabrics

- DynaGlide soleplate for easy gliding on all garments

Comfortable ironing

- Slim-tip soleplate reaches easily into tricky areas
- Button groove speeds up ironing along buttons and seams
- Comfortable handle with texturing for easy grip
- Cord winder for easy cord storage

Full control

- Easy temperature control
- Temperature light indicates when the iron is hot enough



asimpleswitch.com


Highlights

DynaGlide soleplate




DynaGlide coating is one of the best Philips soleplate coatings. It is much more scratch-resistant and it glides better than an aluminium, non-stick or ceramic soleplate.

Slim-tip soleplate



The slim tip of the soleplate allows you to reach easily into the trickiest areas, such as between the buttons, in pleats and in the corners.

Button groove



Button groove speeds up ironing along buttons and seams.

Comfortable handle



The texturing on the handle of the iron ensures a comfortable and ergonomic grip, so that your hand fits well and does not slip during ironing.

Easy storage




The cord can be wrapped around the heel rest so that the appliance is easy to store.

Easy temperature control



An elevated temperature control is easy to operate and precise. You will always have the right temperature for your garment.

Temperature light indicator



Temperature light goes on when the iron is heating up and goes off when the soleplate temperature has reached the set level.



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas — Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Full control

Easy temperature control
Temperature light indicator

Comfortable ironing

Cord length: 1.8 m

Easy to use

Easy to set up and store: Easy cord and hose storage
Long-lasting cord
Reaching tricky areas: Button groove
Soft grip

Fast and powerful crease removal

Power: 1200 W
Soleplate: DynaGlide

