

PHILIPS

Steam iron

1900 series

Steam 22g/min;80g steam boost

Ceramic soleplate

Anti-calc

1450 Watts



GC1990



Faster – from start to finish

Super fast water filling and emptying

There's so much more to life than household chores, so you want to get them done as quickly as possible. With its super fast filling and emptying hole, pointed tip, and smooth-gliding soleplate, this quality iron is simply built for speed.

Easily removes creases

- Steam boost to remove stubborn creases easily

Easy gliding on all fabrics

- Ceramic soleplate for better gliding performance

Longer lifetime

- Double Active Calc System prevents scale build-up

Safe ironing

- Electronic shut-off when iron is left unattended

Faster set-up and storage

- Easy and super fast filling of the watertank
- Easy and super fast emptying of the watertank



asimpleswitch.com

Highlights

Double Active Calc System




Double Active Calc system of your Philips steam iron prevents scale build-up through anti scale pills and an easy to use calc clean function.

Auto shut-off



The electronic shut-off automatically switches the iron off when it is left unattended or tips over.

Steam boost



Steam boost to remove stubborn creases easily.

Ceramic soleplate



Ceramic soleplate is scratch resistant, glides well and easy to clean.

Easy and super fast emptying



Easy and super fast emptying of the watertank thanks to the huge emptying hole, and the sideways opening door.

Easy and super fast filling



Easy and super fast filling of the watertank thanks to the huge filling hole, and the sideways opening door of the Philips iron.

Specifications

Fast & powerful crease removal

Soleplate: Ceramic
 Steam output
 Continuous steam output: 22 g/min
 Steam boost: 80 g
 Vertical steaming
 Variable steam settings
 Spray
 Steam tip
 Power: 1450 W

Easy to use

Water tank capacity: 180 ml
 Filling and emptying water: Sideways opening door, Extra large filling hole
 Safety auto off
 Power cord length: 1.8 m
 Cord freedom (swivel): 180 degree cord freedom

Calc management

Suitable for tap water
 Calc clean solution: Double active calc clean

Technical specifications

Weight of iron: 1.06 kg
 Product dimensions: 26.1 x 11.5 x 13.6 cm
 Voltage: 220 V



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.