

# PHILIPS

## Steam iron

### EasySpeed

Steam 40g/min; 130g steam boost

Non-stick soleplate

Anti-calc

2300 Watts

GC2041/20



## Fast, from start to finish

### 3 ways to speed up your ironing

The EasySpeed steam iron speeds up your ironing thanks to its triple precision tip, even heat distribution across the soleplate and continuous steam.

#### Comfortable ironing

- A fine spray evenly moistens the fabric
- Drip-stop system keeps your garments spotless while ironing
- Even steam distribution for efficient ironing
- Triple precision tip for optimal control and visibility

#### Longer lifetime

- Calc clean slider to easily remove scale out of your iron

#### Easily removes creases

- Continuous steam output up to 40 g/min
- Vertical steam for crease removal in hanging fabrics
- 130 g steam boost to remove stubborn creases easily
- Non-stick soleplate coating
- Power up to 2300 W enabling constant high steam output


# Highlights

## Non-stick soleplate



The soleplate of your Philips iron is coated with a special non-stick layer for good gliding performance on all fabrics.

## Vertical steam



This Philips iron has a vertical steam function, for crease removal in hanging fabrics.

## Calc clean slider



This steam iron can be operated with normal tap water, and the calc clean slider makes it easy to remove any built-up scale from your iron. To maintain the performance of your

Philips steam iron, you should use this scale clean function once a month when using normal tap water.

## Drip stop system



Drip-Stop system lets you iron delicate fabrics at low temperatures without having to worry about stains from water droplets.

## Triple precision tip



The tip of this Philips iron is precise in 3 ways: it has a pointed tip, button groove and a sleek nose design. The triple precision tip enables you to reach even the most tricky areas, e.g. around the buttons or between the pleats.

## Even steam distribution

Thanks to the carefully crafted soleplate design, the steam is distributed evenly across the soleplate. This way you need fewer strokes to evenly moisten the garment and therefore less time to complete the ironing.

## Spray



The spray function produces a fine mist that evenly moistens the fabric, making it easier to iron out creases.

## Up to 40 g/min of steam



The Philips steam iron with continuous steam output of up to 40 g/min gives you the perfect amount of steam to efficiently remove all creases.

## Power up to 2300 W

Power up to 2300 W enables constant high steam output.

## Steam boost up to 130 g

The steam boost can be used for vertical steaming and tough creases.

# Specifications

## Fast crease removal

Variable steam levels  
Vertical steam  
Water spray

## Easy to use

Soleplate name: Non-stick  
Water tank capacity: 270 ml  
Power cord length: 1.8 m  
Drip stop

## Fast and powerful crease removal

Continuous steam output: 40 g/min  
Power: 2300 W  
Steam boost: 130 g

## Scale management

Descaling and cleaning: Easy De-calc

