

Steam iron with Non-stick soleplate

- Steam 40g/min; 130g steam boost
- Non-stick soleplate
- Anti-calc
- 2300 Watts

GC2041/20

## Fast, from start to finish

### 3 ways to speed up your ironing

The EasySpeed iron speeds up your ironing thanks to: triple precision tip, even heat distribution across the soleplate and continuous steam.

#### Benefits

##### Comfortable ironing

- Drip-stop system keeps your garments spotless while ironing
- Triple precision tip for optimal control and visibility
- Even steam distribution for efficient ironing
- A fine spray evenly moistens the fabric

##### Longer lifetime

- Calc clean slider to easily remove scale out of your iron

##### Easily removes creases

- Non-stick soleplate coating
- Vertical steam for crease removal in hanging fabrics
- Continuous steam output up to 40 g/min
- Power up to 2300 W enabling constant high steam output
- 130 g steam boost to remove stubborn creases easily

**PHILIPS**


## Features

### Non-stick soleplate



The soleplate of your Philips iron is coated with a special non-stick layer for good gliding performance on all fabrics.

### Vertical steam



This Philips iron has a vertical steam function, for crease removal in hanging fabrics.

### Calc clean slider



This steam iron can be operated with normal tap water, and the calc clean slider makes it easy to remove any built-up scale from your iron. To maintain the performance of your Philips steam iron, you should use this scale clean function once a month when using normal tap water.

### Drip stop system



Drip-Stop system lets you iron delicate fabrics at low temperatures without having to worry about stains from water droplets.

### Triple precision tip



The tip of this Philips iron is precise in 3 ways: it has a pointed tip, button groove and a sleek nose design. The triple precision tip enables you to reach even the most tricky areas, e.g. around the buttons or between the pleats.

### Even steam distribution

Thanks to the carefully crafted soleplate design, the steam is distributed evenly across the soleplate. This way you need fewer strokes to evenly moisten the garment and therefore less time to complete the ironing.

### Spray



The spray function produces a fine mist that evenly moistens the fabric, making it easier to iron out creases.

### Up to 40 g/min of steam



The Philips steam iron with continuous steam output of up to 40 g/min gives you the perfect amount of steam to efficiently remove all creases.

### Power up to 2300 W

Power up to 2300 W enables constant high steam output.

### Steam boost up to 130 g

The steam boost can be used for vertical steaming and tough creases.

## Specifications

Please note that this is a pre-sales leaflet. The contents of this leaflet reflect the best of our knowledge per date and country mentioned above. The contents of this leaflet are subject to change without notice. Philips does not accept any liability as to the contents of this leaflet.

### Fast crease removal

Variable steam levels	Yes
Vertical steam	Yes
Water spray	Yes

### Easy to use

Soleplate name	Non-stick
Water tank capacity	270 ml
Power cord length	1.8 m
Drip stop	Yes

### Fast and powerful crease removal

Continuous steam output	40 g/min
Power	2300 W
Steam boost	130 g

### Scale management

Descaling and cleaning	Easy De-calc
------------------------	--------------

### Packaging dimensions

Height	16.00 cm
Width	32.00 cm

## EasySpeed

Depth	14.00 cm
Net weight	1.15 kg
Gross weight	1.43 kg
EAN	08710103806899
Number of products included	1
Country of origin	CN
Harmonised Systems Code	851640

### Outer Carton

Length	43.00 cm
Width	32.50 cm
Height	34.00 cm
Gross weight	9.13 kg
EAN	18710103806896
Number of consumer packages	6



data subject to change  
2017, February 18

Version: 2.0.1  
EAN: 08710103806899

© 2017 Koninklijke Philips N.V.  
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. or their respective owners.

[www.philips.com](http://www.philips.com)