

PHILIPS

Cordless steam iron

Easyspeed plus cordless

Steam 35g/min;150g steam boost

Ceramic soleplate

Safety Auto off + Anti-calc

2400 Watts



GC2088/30



Faster cordless ironing, from start to finish

With compact SmartCharging base and light feedback

Faster to set up

- Power up to 2400 W for faster heat-up time
- Iron with smart light feedback indicator

Faster to iron

- Continuous steam up to 35 g/min for better crease removal
- 150 g steam boost to remove stubborn creases easily
- The charging base charges the iron in less than 6 seconds
- Ceramic soleplate for better gliding performance

Faster to store

- Cord winder for easy cord storage
- Lock and carry the iron for stable storage after ironing

Highlights

Quick heat up**2400 W**

Power up to 2400 W for faster heat-up time

Smart light feedback

Smart light feedback indicates the status of the iron at any time.

Up to 35 g/min of steam

Continuous steam up to 35 g/min for better crease removal.

Steam boost up to 150 g

The iron's 150 g steam boost enables you to easily remove even the most stubborn creases.

Compact smart charging base

The compact Smart charging base enables a powerful cordless steam performance. Enjoy the ultimate freedom of movement without changing your ironing pattern: the iron will charge itself on the compac smart charging base while you rearrange the garment . To ensure constant steam performance the smart charging base will indicate with a yellowlight to recharge the iron and ensures the iron will get fully charged in less than 6 seconds. The blue light indicates that the iron is ready to use

Ceramic soleplate

Ceramic soleplate is scratch resistant, glides well and easy to clean.

Easy storage

The cord can be wrapped around the heel rest, so that the appliance is easy to store.

Carry lock

Safe storage after ironing on the base. The cord can be wrapped around the body of the base, so that the appliance is easy to store.

Specifications

Fast & powerful crease removal**Soleplate:** Ceramic, SteamGlide**Continuous steam output:** 35 g/min**Steam boost:** 150 g**Power:** 2400 W**Spray****Variable steam settings****Vertical steaming****Drip stop****Power cord length:** 1.8 m**Safety auto off****Water tank capacity:** 270 ml**Easy to use****Storage solution:** Carry lock**Cord storage:** Cord storage compartment**Intelligent Light feedback**