

PHILIPS

Steam iron

EasySpeed Plus

2100 W

110g steam boost

30g/min continuous steam

Ceramic soleplate



GC2145/24



Fast from start to finish

Speeds up your ironing in 3 ways

EasySpeed Plus speeds up ironing with powerful bursts of steam to tackle tough creases, a durable ceramic soleplate for easy gliding, and our drip-stop system to prevent leakage. That's three easy ways to make fast work of your ironing.

Fast crease removal

- 2100 W to heat up quickly
- Up to 110 g steam boost blasts stubborn creases
- Steam output up to 30 g/min for strong, steady performance
- Durable ceramic soleplate for easy gliding

Easy ironing

- Drip-stop system keeps garments spotless while ironing
- Triple precision tip for optimal control and visibility
- Large 270 ml water tank for ironing more clothes in one go
- Vertical steaming for hanging fabrics

Long lasting performance

- Calc-clean slider for long-lasting steam performance

Highlights

2100 W to heat up quickly



Delivers a fast warm-up and powerful performance.

Steam boost up to 110 g



Penetrates deeper into fabrics to easily remove stubborn creases.

Up to 30 g/min of steam



Strong and consistent steam output to remove creases faster.

Ceramic soleplate



Our durable ceramic soleplate glides well on any ironable garment. It's non-stick, scratch resistant and simple to keep clean.

Drip-stop system



Our drip-stop system prevents leakage to avoid stains from water droplets — and iron with confidence at any temperature.

Triple precision tip



The tip is precise in 3 ways. It has a pointed tip, button groove and sleek nose design. Our triple precision tip helps you handle even the hardest-to-iron spots, like buttons and pleats.

270 ml water tank



Less refilling with the large 270 ml water tank so you can iron more clothes in one go

Vertical steam



The vertical steam function lets you refresh garments right on the hanger and remove creases from curtains as they hang. No ironing board required.

Built-in calc-clean slider



This iron operates with ordinary tap water. Calc-clean is a built-in cleaning function to remove calcium buildup, or limescale, and maintain peak performance.

Specifications

Fast crease removal

Continuous steam: 30 g/min

Power: 2100 W

Steam boost: 110 g

Easy to use

Soleplate name: Ceramic

Water tank capacity: 270 ml

Power cord length: 1.8 m

Scale management

Descaling and cleaning: Built-in Calc Clean

Slider

Green efficiency

User manual: 100% recycled paper

Design

Color: Blue

