



Steam iron

- 2400 W
- 150 g steam boost
- 30 g/min continuous steam
- Ceramic soleplate

GC2145/29

Fast from start to finish

Speeds up your ironing in 3 ways

EasySpeed Plus speeds up ironing with powerful bursts of steam to tackle tough creases, a durable ceramic soleplate for easy gliding and our drip-stop system to prevent leakage. That's three easy ways to make fast work of your ironing.

Benefits

Fast crease removal

- 2400 W to heat up quickly
- Up to 150 g steam boost blasts stubborn creases
- Steam output up to 30 g/min for strong, steady performance
- Durable ceramic soleplate for easy gliding

Easy ironing

- Drip-stop system keeps garments spotless while ironing

- Triple precision tip for optimal control and visibility
- Extra-long 2.5 metre cord for easy reach
- Vertical steaming for hanging fabrics

Long-lasting performance

- Calc-clean slider for long-lasting steam performance

PHILIPS

Features

2400 W to heat up quickly



Delivers a fast warm-up and powerful performance.

Steam boost up to 150 g



Penetrates deeper into fabrics to easily remove stubborn creases.

Up to 30 g/min of steam



Strong and consistent steam output to remove creases faster.

Ceramic soleplate



Our durable ceramic soleplate glides well on any ironable garment. It's non-stick, scratch resistant and simple to keep clean.

Drip-stop system



Our drip-stop system prevents leakage to avoid stains from water droplets — and iron with confidence at any temperature.

Triple precision tip



The tip is precise in 3 ways. It has a pointed tip, button groove and sleek nose design. Our triple precision tip helps you handle even the hardest-to-iron spots, like buttons and pleats.

Extra-long 2.5 m cord



An extra-long 2.5 metre cord provides maximum reach to anywhere on the ironing board and convenience.

Vertical steam



The vertical steam function lets you refresh garments right on the hanger and remove creases from curtains as they hang. No ironing board required.

Built-in calc-clean slider



This iron operates with ordinary tap water. Calc-clean is a built-in cleaning function to remove calcium build-up, or lime scale, and maintain peak performance.

Specifications

Please note that this is a pre-sales leaflet. The contents of this leaflet reflect the best of our knowledge per date and country mentioned above. The contents of this leaflet are subject to change without notice. Philips does not accept any liability as to the contents of this leaflet.

Fast crease removal

Continuous steam	30 g/min
Power	2400 W
Steam boost	150 g

Easy to use

Soleplate name	Ceramic
Water tank capacity	270 ml
Power cord length	2.5 m

EasySpeed Plus

Scale management

Descaling and cleaning Built-in Calc-Clean Slider

Green efficiency

User manual 100% recycled paper

Design

Colour Blue

Packaging dimensions

Height 16.00 cm
Width 30.50 cm
Depth 13.00 cm
Net weight 1.10 kg
Gross weight 1.26 kg

EAN 08710103870159
Number of products included 1
Country of origin CN
Harmonised Systems Code 851640

Outer Carton

Length 53.80 cm
Width 31.70 cm
Height 33.60 cm
Gross weight 10.68 kg
EAN 18710103870156
Number of consumer packages 8



data subject to change
2018, October 29

Version: 4.0.1
EAN: 08710103870159

© 2018 Koninklijke Philips N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. or their respective owners.

www.philips.com