



#### Steam iron

- 2400 W
- 150 g steam boost
- 30 g/min continuous steam
- Ceramic soleplate

GC2147/49

## Fast from start to finish

Speeds up your ironing in 3 ways

EasySpeed Plus speeds up ironing with powerful bursts of steam to tackle tough creases, a durable ceramic soleplate for easy gliding and our drip-stop system to prevent leakage. That's three easy ways to make fast work of your ironing.

#### Benefits

##### Fast crease removal

- 2400 W to heat up quickly
- Steam output up to 30 g/min for strong, steady performance
- Up to 150 g steam boost blasts stubborn creases
- Durable ceramic soleplate for easy gliding

##### Easy ironing

- Drip-stop system keeps garments spotless while ironing

- Large 270 ml water tank for ironing more clothes in one go
- Vertical steaming for hanging fabrics
- Triple precision tip for optimal control and visibility

##### Long-lasting performance

- Calc-clean slider for long-lasting steam performance

**PHILIPS**

## Features

### 2400 W to heat up quickly



Delivers a fast warm-up and powerful performance.

### Drip-stop system



Our drip-stop system prevents leakage to avoid stains from water droplets — and iron with confidence at any temperature.

### 270 ml water tank



Less refilling with the large 270 ml water tank so you can iron more clothes in one go

### Vertical steam



The vertical steam function lets you refresh garments right on the hanger and remove creases from curtains as they hang. No ironing board required.

### Built-in calc-clean slider



This iron operates with ordinary tap water. Calc-clean is a built-in cleaning function to remove calcium build-up, or lime scale, and maintain peak performance.

### Up to 30 g/min of steam



Strong and consistent steam output to remove creases faster.

### Steam boost up to 150 g



Penetrates deeper into fabrics to easily remove stubborn creases.

### Ceramic soleplate



Our durable ceramic soleplate glides well on any ironable garment. It's non-stick, scratch resistant and simple to keep clean.

### Triple precision tip



The tip is precise in 3 ways. It has a pointed tip, button groove and sleek nose design. Our triple precision tip helps you handle even the hardest-to-iron spots, like buttons and pleats.

## Specifications

Please note that this is a pre-sales leaflet. The contents of this leaflet reflect the best of our knowledge per date and country mentioned above. The contents of this leaflet are subject to change without notice. Philips does not accept any liability as to the contents of this leaflet.

### Fast crease removal

Continuous steam 30 g/min  
Power 2400 W

Steam boost 150 g

## EasySpeed Plus

### Easy to use

Soleplate name	Ceramic
Water tank capacity	270 ml
Power cord length	2.5 m

### Scale management

Descaling and cleaning	Built-in Calc-Clean Slider
------------------------	----------------------------

### Green efficiency

User manual	100% recycled paper
-------------	---------------------

### Packaging dimensions

Height	16.00 cm
Width	30.50 cm
Depth	13.00 cm
Net weight	1.10 kg

Gross weight	1.26 kg
EAN	08710103875109
Number of products included	1
Country of origin	CN
Harmonised Systems Code	851640

### Outer Carton

Length	53.80 cm
Width	31.70 cm
Height	33.60 cm
Gross weight	10.68 kg
EAN	18710103875106
Number of consumer packages	8



data subject to change  
2018, April 28

Version: 1.0.1  
EAN: 08710103875109

© 2018 Koninklijke Philips N.V.  
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. or their respective owners.

[www.philips.com](http://www.philips.com)