

PHILIPS

Steam iron


EasySpeed Advanced

2400 W

180 g steam boost

40 g/min continuous steam

Ceramic soleplate



GC2673/89



Faster from start to finish

Speeds up your ironing in 5 ways

Make ironing faster from start to finish: quick heat-up, XL water hole, powerful bursts of steam to tackle tough creases, durable ceramic soleplate for quick gliding and our drip-stop system. That's five ways to speed up your ironing.

Fast ironing

- 2400 W for quick heat-up in 30 seconds
- Extra-large water hole for fast filling and emptying
- Up to 180 g steam boost blasts stubborn creases
- Continuous steam output up to 40 g/min
- Triple precision tip for optimal control and visibility

Easy ironing

- Drip-stop system keeps garments spotless while ironing
- Durable ceramic soleplate for easy gliding
- Easy cord wrapping with clip for quick, tidy storage
- Less refilling with extra-large 300 ml water tank

Long-lasting performance

- Calc-clean slider for long-lasting steam performance

Highlights

2400 W to heat up quickly



Delivers a fast warm-up in 30 seconds for a quick start.

XL water filling hole



An extra-large opening for filling the water tank makes quick work of refills and emptying.

Steam boost up to 180 g




Penetrates deeper into fabrics to easily remove stubborn creases.

Up to 40 g/min of steam



The Philips steam iron with continuous steam output of up to 40 g/min gives you the perfect amount of steam to efficiently remove all creases.

Triple precision tip



The tip is precise in 3 ways. It has a pointed tip, button groove and sleek nose design. Our triple precision tip helps you handle even the hardest-to-iron spots, like buttons and pleats.

Drip-stop system



Our drip-stop system prevents leakage to avoid stains from water droplets — and iron with confidence at any temperature.

Ceramic soleplate



Our durable ceramic soleplate glides well on any ironable garment. It's non-stick, scratch resistant and simple to keep clean.

Cord wrapping with clip



The cord is easily wrapped around the base of the iron and held in place with a clip for tidy storage.

300 ml water tank



Fewer refills are required thanks to a large 300 ml water tank so you can iron more clothes in one go.

Built-in calc-clean slider



This iron operates with ordinary tap water. Calc-clean is a built-in cleaning function to remove calcium build-up, or lime scale, and maintain peak performance.

Specifications

Fast crease removal

Continuous steam: 40 g/min
Power: 2400 W
Steam boost: 180 g
Variable steam levels
Vertical steam
Water spray

Easy to use

Soleplate name: Ceramic
Water tank capacity: 300 ml
Cord freedom (swivel): 360 degree cord freedom

Power cord length: 2.5 m
Precision steam tip
Tap water suitable
Drip-stop
Extra-large filling hole

Scale management

Descaling and cleaning: Self-clean

Storage

Cord storage: Cord clip

Size and weight

Weight of iron: 1.150 kg

Guarantee

2 year worldwide guarantee

Green efficiency

Energy saving mode
User manual: 100% recycled paper

Technical specifications

Heating time: 30 sec.

