



Steam iron

- 2400 W
- 180 g steam boost
- 40 g/min continuous steam
- Ceramic soleplate

GC2673/89

Faster from start to finish

Speeds up your ironing in 5 ways

Make ironing faster from start to finish: quick heat-up, XL water hole, powerful bursts of steam to tackle tough creases, durable ceramic soleplate for quick gliding and our drip-stop system. That's five ways to speed up your ironing.

Benefits

Fast ironing

- 2400 W for quick heat-up in 30 seconds
- Extra-large water hole for fast filling and emptying
- Up to 180 g steam boost blasts stubborn creases
- Continuous steam output up to 40 g/min
- Triple precision tip for optimal control and visibility

Easy ironing

- Drip-stop system keeps garments spotless while ironing

- Durable ceramic soleplate for easy gliding
- Easy cord wrapping with clip for quick, tidy storage
- Less refilling with extra-large 300 ml water tank

Long-lasting performance

- Calc-clean slider for long-lasting steam performance

PHILIPS

Features

2400 W to heat up quickly



Delivers a fast warm-up in 30 seconds for a quick start.

XL water filling hole



An extra-large opening for filling the water tank makes quick work of refills and emptying.

Steam boost up to 180 g



Penetrates deeper into fabrics to easily remove stubborn creases.

Up to 40 g/min of steam



The Philips steam iron with continuous steam output of up to 40 g/min gives you the perfect amount of steam to efficiently remove all creases.

Triple precision tip



The tip is precise in 3 ways. It has a pointed tip, button groove and sleek nose design. Our triple precision tip helps you handle even the hardest-to-iron spots, like buttons and pleats.

Drip-stop system



Our drip-stop system prevents leakage to avoid stains from water droplets — and iron with confidence at any temperature.

Ceramic soleplate



Our durable ceramic soleplate glides well on any ironable garment. It's non-stick, scratch resistant and simple to keep clean.

Cord wrapping with clip



The cord is easily wrapped around the base of the iron and held in place with a clip for tidy storage.

300 ml water tank



Fewer refills are required thanks to a large 300 ml water tank so you can iron more clothes in one go.

Built-in calc-clean slider



This iron operates with ordinary tap water. Calc-clean is a built-in cleaning function to remove calcium build-up, or lime scale, and maintain peak performance.

Specifications

Please note that this is a pre-sales leaflet. The contents of this leaflet reflect the best of our knowledge per date and country mentioned above. The contents of this leaflet are subject to change without notice. Philips does not accept any liability as to the contents of this leaflet.

Fast crease removal

Continuous steam 40 g/min
Power 2400 W

Steam boost 180 g
Variable steam levels Yes
Vertical steam Yes

EasySpeed Advanced

Water spray Yes

User manual 100% recycled paper

Easy to use

Soleplate name Ceramic
Water tank capacity 300 ml
Cord freedom (swivel) 360 degree cord freedom
Power cord length 2.5 m
Precision steam tip Yes
Tap water suitable Yes
Drip-stop Yes
Extra-large filling hole Yes

Technical specifications

Heating time 30 sec.

Packaging dimensions

Height 16.00 cm
Width 31.50 cm
Depth 14.00 cm
Net weight 1.24 kg
Gross weight 1.48 kg
EAN 08710103872054
Number of products included 1
Country of origin CN
Harmonised Systems Code 851640

Scale management

Descaling and cleaning Self-clean

Outer Carton

Length 43.00 cm
Width 32.50 cm
Height 34.00 cm
Gross weight 9.43 kg
EAN 18710103872051
Number of consumer packages 6

Storage

Cord storage Cord clip

Size and weight

Weight of iron 1.150 kg

Guarantee

2 year worldwide guarantee Yes

Green efficiency

Energy saving mode Yes



data subject to change
2018, June 23

Version: 4.0.1
EAN: 08710103872054

© 2018 Koninklijke Philips N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. or their respective owners.

www.philips.com